Product data sheet

Specifications





TeSys Deca reversing contactor -3P(3 NO) - AC-3 - <= 440 V 40 A -24 V DC coil

LC2D40ABD

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 692.00 USD

Μ	ai	n
141	a	

mann	
Range	TeSys
C	TeSys Deca
	·
Product Name	TeSys Deca
	TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Motor control
	Resistive load
Utilisation Category	AC-3
ounsation category	AC-3 AC-1
	AC-3e
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
	510
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25400 Hz Power circuit <= 300 V DC
[le] Rated Operational Current	40 A (at <140 °F (60 °C)) at <= 440 V AC AC-3 for power circuit
	60 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
	40 A (at <140 °F (60 °C)) at <= 440 V AC AC-3e for power circuit
Motor Power Kw	11 kW at 220230 V AC 50-60 Hz
	18.5 kW at 380400 V AC 50-60 Hz
	22 kW at 415 V AC 50-60 Hz
	22 kW at 440 V AC 50-60 Hz
	22 kW at 500 V AC 50-60 Hz
	30 kW at 660690 V AC 50-60 Hz
Motor Bower Hp (III / Caa)	
Motor Power Hp (UI / Csa)	5 hp at 230/240 V AC 60 Hz for 1 phase motors
	10 hp at 230/240 V AC 60 Hz for 3 phase motors 30 hp at 575/600 V AC 60 Hz for 3 phase motors
	10 hp at 200/208 V AC 60 Hz for 3 phase motors
	3 hp at 115 V AC 60 Hz for 1 phase motors
	30 hp at 460/480 V AC 60 Hz for 3 phase motors
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	24 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air	10 A (at 140 °F (60 °C)) for signalling circuit
Thermal Current	60 A (at 140 °F (60 °C)) for power circuit
	// .

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
	800 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	800 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	72 A 104 °F (40 °C) - 10 min for power circuit
Current	165 A 104 °F (40 °C) - 1 min for power circuit
	320 A 104 °F (40 °C) - 10 s for power circuit
	720 A 104 °F (40 °C) - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
0	80 A gG at <= 690 V coordination type 1 for power circuit
	80 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 60 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit 690 V IEC 60947-4-1
	Power circuit 600 V CSA
	Power circuit 600 V UL
	Signalling circuit 690 V IEC 60947-1
	Signalling circuit 600 V CSA
	Signalling circuit 600 V UL
Electrical Durability	1.5 Mcycles 40 A AC-3 <= 440 V
	0.7 Mcycles 60 A AC-1 <= 440 V
	1.5 Mcycles 40 A AC-3e <= 440 V
Power Dissipation Per Pole	2.4 W AC-3
	5.4 W AC-1
	2.4 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Plate
	Rail
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	UL
	CSA
	RINA
	GOST
	DNV
	LROS (Lloyds register of shipping)
	GL
	BV
	UKCA

Connections - Terminals	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible without cable end
	Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)flexible without cable end
	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)flexible with cable end
	Control circuit screw clamp terminals 2 0.000.00 in ² (12.5 mm ²)flexible with cable end
	Control circuit screw clamp terminals 1 0.000.01 in ² (14 mm ²)solid
	Control circuit screw clamp terminals 2 0.000.01 in ² (14 mm ²)solid
	Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²)flexible without cable end
	Power circuit EverLink BTR screw connectors 2 0.000.04 in ² (125 mm ²)flexible without cable end
	Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²)flexible with cable end
	Power circuit EverLink BTR screw connectors 2 0.000.04 in ² (125 mm ²)flexible with cable end
	Power circuit EverLink BTR screw connectors 1 0.000.05 in ² (135 mm ²)solid Power circuit EverLink BTR screw connectors 2 0.000.04 in ² (125 mm ²)solid
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals flat Ø 6 mm
	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Philips No 2
	Power circuit 70.81 lbf.in (8 N.m) EverLink BTR screw connectors 0.040.05 in ²
	(2535 mm ²) hexagonal 0.16 in (4 mm) Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors 0.000.04 in ² (1
	25 mm²) hexagonal 0.16 in (4 mm) Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals pozidriv No 2
	Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals pozidriv No 2
Operating Time	1624 ms opening
	42.557.5 ms closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

Complementary

Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.3 Uc -40158 °F (-4070 °C) drop-out DC 0.751.25 Uc -40140 °F (-4060 °C) operational DC 11.25 Uc 140158 °F (6070 °C) operational DC
Time Constant	34 ms
Inrush Power In W	19 W 68 °F (20 °C))
Hold-In Power Consumption In W	7.4 W 68 °F (20 °C)
Auxiliary Contacts Type	Mechanically linked 1 NO + 1 NC IEC 60947-5-1 Mirror contact 1 NC IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

Environment

Ip Degree Of Protection	IP20 front face IEC 60529
Climatic Withstand	IACS E10 IEC 60947-1 Annex Q category D
Protective Treatment	TH IEC 60068-2-30

Pollution Degree	3
Ambient Air Temperature For Operation	-40140 °F (-4060 °C) 140158 °F (6070 °C) with derating
Ambient Air Temperature For Storage	-76176 °F (-6080 °C)
Operating Altitude	09842.52 ft (03000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open2 Gn, 5300 Hz Vibrations contactor closed4 Gn, 5300 Hz Shocks contactor open10 Gn for 11 ms Shocks contactor closed15 Gn for 11 ms
Height	4.80 in (122 mm)
Width	4.69 in (119 mm)
Depth	4.72 in (120 mm)
Net Weight	4.45 lb(US) (2.02 kg)

Ordering and shipping details

Category	US10I1222358
Discount Schedule	0112
Gtin	3389118340923
Returnability	No
Country Of Origin	FR

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14.0 cm)
Package 1 Width	6.38 in (16.2 cm)
Package 1 Length	7.80 in (19.8 cm)
Package 1 Weight	4.78 lb(US) (2.168 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards


REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Dimensions





Product data sheet

Connections and Schema

Wiring

