





Circuit breaker, PowerPacT L, 400A, 3 pole, 600VAC, 14kA, I-Line, MicroLogic 6.3E, 100%, ABC

LDA36400CU54X

### Main

Range	PowerPact	
Product Name	PowerPact L	
Device Short Name	L-Frame	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Complementary	
Line Rated Current	400 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 240 V AC 50/60 Hz UL 489 18 kA 480 V AC 50/60 Hz UL 489 14 kA 600 V AC 50/60 Hz UL 489 20 kA 250 V DC UL 489
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz IEC 60947-3
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220/240 V AC 50/60 Hz IEC 60947-2 18 kA 380/440/415 V AC 50/60 Hz IEC 60947-2 14 kA 500/525 V AC 50/60 Hz IEC 60947-2 20 kA 250 V DC IEC 60947-2 20 kA 500 V DC IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, energy, MicroLogic 6.3 E, LSIG
Continuous Current Rating	100 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 6.3 E
Protection Technology	Current limiter
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A
Awg Gauge	2 x AWG 2/0500 kcmil aluminium/copper
Local Signalling	Ready 1 LED green) Alarm 1 LED 90 % Ir orange) Alarm LED 105 % Ir red) Switched off (OFF) 1 trip indicator green)
Mounting Mode	I-Line bracket)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Support	Bracket	
Electrical Connection	I-Line connection, line Lugs, load	
Terminal Identifier	AL600LS52K3	
Long Time Pick-Up Adjustment Range	0.251 x ln	
Mounting Height	6 in (152.40 mm)	
Tightening Torque	442.54 lbf.in (50 N.m) 0.110.37 in² (70240 mm²) (AWG 2/0500 kcmil)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	1.22 in (31 mm) 2.40 in (61 mm)	
Color	Black	
Height	13.39 in (340 mm)	
Width	5.51 in (140 mm)	
Depth	4.33 in (110 mm)	
Net Weight	13.67 lb(US) (6.2 kg)	
Phase Connection	ABC	
Communication Interface	on Interface Modbus Ethernet	
Circuit Breaker Application	HACR rated	

### **Environment**

Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2	
Product Certifications	UL CSA NOM	
Ip Degree Of Protection	Front cover IP40	
Pollution Degree	3 IEC 60947-1	
Ambient Air Temperature For Operation	28158 °F (-270 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	< 6561.68 ft (2000 m) without derating 5000 m with derating	

# Ordering and shipping details

Category	01118-L ELEC TRIP I-LINE BREAKER/SW	
Discount Schedule	DE2	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	14.69 in (37.3 cm)
Package 1 Width	5.94 in (15.1 cm)
Package 1 Length	6.61 in (16.8 cm)
Package 1 Weight	17.00 lb(US) (7.711 kg)

# **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov