

Product data sheet

Specifications



TeSys LK disconnect switch kit,
disconnect switch, 3 P, 30 A, shaft,
guide cone, red handle, NEMA 1,
3R and 12

LK4DUKR1

! Discontinued

! Discontinued on: Oct 6, 2021

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range	TeSys
Product Or Component Type	Disconnect Switch
Disconnecter Device Type	Non-fusible disconnect switch
Suitability For Isolation	Yes
Handle Colour	Red
Handle Front Plate Colour	Yellow

Complementary

Poles Description	3P
Network Type	AC
Network Frequency	50/60 Hz
[Ie] Rated Operational Current	30 A600 V AC UL 30 A600 V AC CSA 32 A400 V AC AC-22A IEC 32 A400 V AC AC-23A IEC 32 A690 V AC AC-22A IEC 32 A690 V AC AC-23A IEC
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz
Rated Power In W	15 kW 400 V 18.5 kW 500 V 25 kW 690 V
Rated Power In Hp	10 hp 240 V 30 A AC 20 hp 480 V 28 A AC 25 hp 600 V 28 A AC
[Icw] Rated Short-Time Withstand Current	5.5 kA
Mechanical Durability	10000 cycles
Electrical Durability	6000 cycles
Connections - Terminals	Lugs-ring terminals 1 0.01 in ² (4 mm ²)
Width	3.13 in (79.5 mm)

Environment

Nema Degree Of Protection	NEMA 1/12/3R
---------------------------	--------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL98 CSA C22.2 No 4 IEC 60947-3
Product Certifications	UL CSA
Height	4.92 in (125 mm)
Depth	2.52 in (64 mm)

Ordering and shipping details

Category	US10I1122640
Discount Schedule	0I11
Gtin	785901733478
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.60 in (9.144 cm)
Package 1 Width	5.50 in (13.97 cm)
Package 1 Length	17.80 in (45.212 cm)
Package 1 Weight	2.46 lb(US) (1.116 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov	