

Product data sheet

Specifications



Contactor, TeSys Deca, 4P(2NO + 2NC), AC-1, <= 440 V 125 A - 48 V DC coil

LP1D80008EW

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LP1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit <= 690 V AC 25...400 Hz Power circuit <= 300 V DC
[Ie] Rated Operational Current	125 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	48 V DC

Complementary

Compatibility Code	LP1D
Pole Contact Composition	2 NO + 2 NC
Contact Compatibility	M4
Protective Cover	Without
[Ith] Conventional Free Air Thermal Current	125 A (at 140 °F (60 °C)) for power circuit
Irms Rated Making Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	135 A 104 °F (40 °C) - 10 min for power circuit 320 A 104 °F (40 °C) - 1 min for power circuit 640 A 104 °F (40 °C) - 10 s for power circuit 990 A 104 °F (40 °C) - 1 s for power circuit
Associated Fuse Rating	200 A gG at <= 690 V coordination type 1 for power circuit 160 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit
Power Dissipation Per Pole	12.5 W AC-1
[Ui] Rated Insulation Voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical Durability	4 Mcycles
Electrical Durability	0.8 Mcycles 125 A AC-1 <= 440 V
Control Circuit Type	DC wide range
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.1...0.3 Uc -40...158 °F (-40...70 °C) drop-out DC 0.75...1.2 Uc -40...131 °F (-40...55 °C) operational DC 1...1.2 Uc 131...158 °F (55...70 °C) operational DC
Inrush Power In W	22 W 68 °F (20 °C))
Hold-In Power Consumption In W	22 W 68 °F (20 °C)
Operating Time	6...20 ms opening 20...35 ms closing
Time Constant	75 ms
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)
Connections - Terminals	Control circuit: screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) - cable stiffness: solid Control circuit: screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) - cable stiffness: solid Power circuit: connector 1 0.01...0.08 in ² (4...50 mm ²) - cable stiffness: flexible without cable end Power circuit: connector 2 0.01...0.04 in ² (4...25 mm ²) - cable stiffness: flexible without cable end Power circuit: connector 1 0.01...0.08 in ² (4...50 mm ²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.01...0.02 in ² (4...16 mm ²) - cable stiffness: flexible with cable end Power circuit: connector 1 0.01...0.08 in ² (4...50 mm ²) - cable stiffness: solid Power circuit: connector 2 0.01...0.04 in ² (4...25 mm ²) - cable stiffness: solid Control circuit: screw clamp terminals 1 0.00...0.00 in ² (1...2.5 mm ²) - cable stiffness: flexible with cable end
Tightening Torque	Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals Philips No 2 Power circuit 106.21 lbf.in (12 N.m) connector flat Ø 6 to Ø 8 mm Power circuit 106.21 lbf.in (12 N.m) connector hexagonal 0.16 in (4 mm)
Mounting Support	Rail Plate

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product Certifications	BV CCC CSA DNV EAC GL LROS (Lloyds register of shipping) UL
Ip Degree Of Protection	IP20 front face IEC 60529

Permissible Ambient Air Temperature Around The Device	-40...140 °F (-40...60 °C) 140...158 °F (60...70 °C) with derating
Operating Altitude	0...9842.52 ft (0...3000 m)
Fire Resistance	1562 °F (850 °C) IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 3 Gn, 5...300 Hz) Shocks contactor open 8 Gn for 11 ms) Shocks contactor closed 10 Gn for 11 ms)
Height	5.00 in (127 mm)
Width	3.78 in (96 mm)
Depth	7.72 in (196 mm)
Net Weight	6.42 lb(US) (2.91 kg)

Ordering and shipping details

Category	22359-CTR,TESYS D,OPEN,80-150A AC&DC
Discount Schedule	I12
Gtin	3389110228434
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.