Product data sheet

Specifications





thermal overload relays, TeSys Deca, 60...100A, class 20

LR9D5567

Product availability: Stock - Normally stocked in distribution facility

Price*: 298.00 USD

Main

Range	TeSys	
Product Name	TeSys LRD TeSys Deca	
Product Or Component Type	Electronic thermal overload relay	
Device Short Name	LR9D	
Relay Application	Motor protection	
Product Compatibility	LC1D150 NSX circuit breaker LC1D115	
Network Type	AC	
Thermal Overload Class	Class 20 IEC 60947-4-1	
Signalling Function	Alarm	
Thermal Protection Adjustment Range	60100 A	
[Ui] Rated Insulation Voltage	Power circuit 1000 V IEC 60947-4-1 Power circuit 600 V CSA Power circuit 600 V UL	

Complementary

Network Frequency	50-60 Hz
[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	1732 V
Mounting Support	Under contactor Rail
Tripping Threshold	1.05 +/- 0.06 In alarm IEC 60947-4-1 1.12 +/- 0.06 In de-energisation IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1
Phase Failure Sensitivity	Tripping in 4 s +/- 20 % IEC 60947-4-1
Control Type	Red push-button stop Blue push-button reset
Temperature Compensation	-4140 °F (-2060 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Switching Capacity In Ma	0150 mA	
Maximum Voltage Drop	<2.5 V closed state	
Connections - Terminals	Power circuit bars Control circuit screw clamp terminals 1 0.000.00 in ² (0.51.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.000.00 in ² (0.51.5 mm ²) flexible without cable end Alarm circuit screw clamp terminals 1 0.000.00 in ² (0.51.5 mm ²) flexible without cable end	
Tightening Torque	Alarm circuit 3.98 lbf.in (0.45 N.m) screw clamp terminals Power circuit 159.31 lbf.in (18 N.m) bars M8 Control circuit 10.62 lbf.in (1.2 N.m) screw clamp terminals	
Height	4.65 in (118 mm)	
Width	4.53 in (115 mm)	
Depth	4.92 in (125 mm)	
Net Weight	1.95 lb(US) (0.885 kg)	

Environment

Climatic Withstand	IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)
Operating Altitude	<= 6561.68 ft (2000 m) without derating
Mechanical Robustness	Vibrations2 Gn, 5300 Hz IEC 60068-2-6 Shocks13 Gn for 11 ms IEC 60068-2-7
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5
Product Certifications	UL CSA CCC UKCA

Ordering and shipping details

Category	US10I1222347	
Discount Schedule	0112	
Gtin	3389110113105	
Returnability	Yes	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	6.10 in (15.5 cm)

Package 1 Length	5.12 in (13.0 cm)	
Package 1 Weight	32.98 oz (935.0 g)	
Unit Type Of Package 2	S04	
Number Of Units In Package 2	12	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	15.75 in (40.0 cm)	
Package 2 Length	23.62 in (60.0 cm)	
Package 2 Weight	26.47 lb(US) (12.005 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov