# **Product data sheet**

Specification





# TeSys Deca thermal overload relays - 9...13 A - class 10A

LRD313

Product availability: Stock - Normally stocked in distribution facility

Price\*: 107.00 USD

#### Main

TeSys TeSys Deca
TeSys LRD TeSys Deca
Differential thermal overload relay
LRD
Motor protection
LC1D40A LC1D50A LC1D65A
AC DC
Class 10A IEC 60947-4-1
913 A
Power circuit 600 V CSA Power circuit 600 V UL Power circuit 690 V IEC 60947-4-1

#### Complementary

Network Frequency	0400 Hz
Mounting Support	Plate, with specific accessories
	Rail, with specific accessories
	Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	0.95 A 380 V AC-15 signalling circuit
	0.06 A 440 V DC-13 signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0400 Hz power circuit IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit
	4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button stop
	Blue push-button reset
Temperature Compensation	-4140 °F (-2060 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Connections - Terminals	Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible without cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) flexible with cable end Control circuit screw clamp terminals 2 0.000.00 in² (12.5 mm²) solid without cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in² (135 mm²) flexible without cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in² (135 mm²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.000.05 in² (135 mm²) solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors
Height	2.76 in (70 mm)
Width	2.17 in (55 mm)
Depth	4.84 in (123 mm)
Net Weight	0.83 lb(US) (0.375 kg)

#### **Environment**

Climatic Withstand	IACS E10	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) without derating IEC 60947-4-1	
Ambient Air Temperature For Storage	-76158 °F (-6070 °C)	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Shocks15 Gn for 11 ms IEC 60068-2-7 Vibrations4 gn IEC 60068-2-6	
Dielectric Strength	tric Strength 1.89 kV 50 Hz IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 EN 50495	
Product Certifications	IEC UL CSA CCC EAC DNV-GL RMRS EU-RO MR LROS (Lloyds register of shipping) ATEX INERIS UKCA	

## Ordering and shipping details

Category	US10I1222347
Discount Schedule	0112
Gtin	3389119215459
Returnability	Yes
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.40 in (6.1 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	5.35 in (13.6 cm)
Package 1 Weight	14.11 oz (400 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	13
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	12.13 lb(US) (5.502 kg)

## **Contractual warranty**

Warranty 18 months

### Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov