Specifications





() Discontinued

plug in relay, Harmony Electromechanical Relays, 15A, 3CO, lockable test button, 12V DC

RPM31JD

(Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Power
Product Or Component Type	Plug-in relay
Device Short Name	RPM
Contacts Type And Composition	3 C/O
[Uc] Control Circuit Voltage	12 V DC
[Ithe] Conventional Enclosed Thermal Current	15 A -40131 °F (-4055 °C)
Status Led	Without
Control Type	Lockable test button
Utilisation Coefficient	20 %

Complementary

Shape Of Pin	Flat
[Ui] Rated Insulation Voltage	250 V IEC
	300 V CSA
	300 V UL
[Uimp] Rated Impulse Withstand Voltage	4 kV 1.2/50 μs
Contacts Material	AgNi
[le] Rated Operational Current	15 A 277 V AC) UL
	15 A 28 V DC) UL
	15 A 250 V AC) NO IEC
	15 A 28 V DC) NO IEC
	7.5 A 250 V AC) NC IEC
	7.5 A 28 V DC) NC IEC
Maximum Switching Voltage	250 V IEC
Resistive Load Current	15 A 250 V AC
	15 A 28 V DC
Maximum Switching Capacity	3750 VA
	420 W
Minimum Switching Capacity	170 mW 10 mA, 17 V
Operating Rate	<= 1200 cycles/hour under load
	<= 18000 cycles/hour no-load
Mechanical Durability	1000000 cycles
Electrical Durability	100000 cycles resistive

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Average Coil Consumption	1.5 W
Drop-Out Voltage Threshold	>= 0.1 Uc DC
Operate Time	20 ms at nominal voltage
Release Time	20 ms at nominal voltage
Average Coil Resistance	80 Ohm at 68 °F (20 °C) +/- 10 %
Rated Operational Voltage Limits	9.613.2 V DC
Protection Category	RTI
Test Levels	Level A group mounting
Operating Position	Any position
Pollution Degree	3
Safety Reliability Data	B10d = 100000
Net Weight	0.12 lb(US) (0.054 kg)
Device Presentation	Complete product

Environment

Dielectric Strength	1500 V AC between contacts with micro disconnection
	2000 V AC between coil and contact with reinforced
	2000 V AC between poles with basic
Standards	EN/IEC 61810-1
	UL 508
	CSA C22.2 No 14
Product Certifications	EAC
	CSA
	UL
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)
Vibration Resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation
	5 gn +/- 1 mm 10…150 Hz)5 cycles not operating
Degree Of Protection (Housing Only)	IP40 conforming to EN/IEC 60529
Shock Resistance	15 gnin operation
	30 gnnot operating

Ordering and shipping details

Category	US10CP221127	
Discount Schedule	0CP2	
Gtin	3389119402026	
Returnability	No	
Country Of Origin	CN	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.85 in (4.7 cm)
Package 1 Width	0.98 in (2.5 cm)
Package 1 Length	1.10 in (2.8 cm)

Package 1 Weight	2.01 oz (57 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.22 in (3.1 cm)
Package 2 Width	4.13 in (10.5 cm)
Package 2 Length	6.89 in (17.5 cm)
Package 2 Weight	20.21 oz (573 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	80
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	11.11 lb(US) (5.04 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc


Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions




Pin Side View



Connections and Schema

Wiring Diagram




Symbols shown in blue correspond to Nema marking.

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor $\cos \phi$)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note : These are typical curves, actual durability depends on load, environment, duty cycle, etc.