





PowerLogic

ION8650 meter 64MB, 9S/29S/ 36S, 277VAC 60Hz, Ethernet No I/

S8650B0C0E6E1A0A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 12,652.90 USD

Main Range

Product Name	PowerLogic ION8650
Device Short Name	ION8650B
Product Or Component Type	Revenue and power quality meter
Complementary	
Power Quality Analysis	harmonic distortion programmablity (logic and math functions) voltage sag and swell detection up to the 63rd harmonic IEC 61000-4-15 flicker transient capture EN 50160 compliance report IEC 61000-4-30 class S power quality measurement
	magnitude harmonic up to the 40th EN 50160 ed. 4 power quality monitoring
Device Application	Tariff metering Instrument transformer correction Energy pulsing and totalisation Co-generation and IPP monitoring Equipment monitoring and control Load curtailment Demand and power factor control
Type Of Measurement	Power factor total Power factor per phase Apparent power total Apparent power per phase Active power total Active power per phase Reactive power total Reactive power per phase Current Voltage Frequency
Supply Voltage	120277 V AC 4763 Hz
Network Frequency	60 Hz
Line Rated Current	5 A 1 A 2 A
Poles Description	3P + N 1P + N 3P
Power Consumption In Va	24 VA
Maximum Power Consumption In Va	33 VA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Display Type	FSTN transflective LCD
Form Designation	9S 3-element 4 36S 2½-element 4 29S 2½-element 4
Sampling Rate	1024 samples/cycle
Measurement Current	0.00124 A
Input Type	Current 0.0120 A (impedance 0.05 Ohm)
Measurement Voltage	57277 V AC phase to neutral 100480 V AC phase to phase
Number Of Inputs	0
Measurement Accuracy	Current 0.1 % Voltage 0.1 % Power 0.1 % Power factor 0.1 % Frequency 0.001 Hz Energy 0.1 %
Accuracy Class	Class 0.2S energy IEC 62053-22 Class 0.2S energy IEC 62053-23 Class 0.2 energy ANSI C12.20
Number Of Outputs	2 pulse
Communication Port Protocol	TCP/IP 10/100 Mbit/s DNP3 300115200 bauds ION 300115200 bauds DLMS 300115200 bauds Modbus 57600 bauds Ansi C12.18 <= 19200 bauds DNP3 10/100 Mbit/s ION 10/100 Mbit/s IEC 61850 ed. 2 10/100 Mbit/s Modbus RTU, master/slave 300115200 bauds Modbus TCP, master/slave 10/100 Mbit/s EtherGate
Communication Port Support	RJ45 ETHERNET SUB-D 9 RS485/RS232 infrared Terminal block RS485
Time Synchronisation Protocol	IRIG-B GPS: Truetime/Datum
Data Recording	Alarms GPS synchronisation Historical logs Event logs Sag and swell logs Time stamping Revenue logs Harmonics logs Data logs
Transmission Rate	57600 bauds 10/100 Mbit/s <= 19200 bauds 300115200 bauds
Memory Capacity	64 MB
Web Services	Alarm notification by e-mail Robust security logs Port addressing user designed Web server
Ethernet Service	SNMP-Traps and SYSLOG Enable/disable Ethernet protocols Enable/disable serial ports
Tamperproof Of Settings	Protected by access code
Compatibility Code	ION8650B

Environment

Electromagnetic Compatibility	Electrostatic discharge immunity test conforming to IEC 61000-4-2 Susceptibility to electromagnetic fields conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 1.2/50 µs shock waves immunity test conforming to IEC 61000-4-5 Conducted and radiated emissions B conforming to CISPR 22 Conducted RF disturbances conforming to IEC 61000-4-6 Immunity to impulse waves conforming to IEC 61000-4-12	
Mounting Mode	Socket-mounted	
Mounting Support	Enclosure door	
Type Of Installation	Indoor installation	
Overvoltage Category	III	
Ip Degree Of Protection	IP65 front face: IP51 back:	
Relative Humidity	595 %	
Pollution Degree	2	
Ambient Air Temperature For Operation	-40185 °F (-4085 °C)	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Operating Altitude	09842.52 ft (03000 m)	
Standards	ANSI C12.1 IEC 62052-11	
Width	7.01 in (178 mm)	
Depth	9.33 in (237 mm)	
Height	7.01 in (178 mm)	
Net Weight	15.43 lb(US) (7 kg)	

Ordering and shipping details

Category	US1PM1S09759	
Discount Schedule	PM1S	
Returnability	No	
Country Of Origin	CA	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.24 in (26.0 cm)
Package 1 Width	11.02 in (28.0 cm)
Package 1 Length	17.32 in (44.0 cm)
Package 1 Weight	9.92 lb(US) (4.5 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov