Product data sheet

Specifications



Circuit breaker frame, MasterPact MTZ2 10H1 drawout for MicroLogic X, 1000A, 66kA/ 415VAC (Icu), 3P

LV848245

Main

MasterPacT	
MasterPact MTZ2	
MTZ2 10 H1	
Circuit breaker	
Power distribution protection	
3P	
Without control unit	
control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi	
1000 A 104 °F (40 °C)	
H1 66 kA 415 V AC	
690 V AC 50/60 Hz	
Yes EN/IEC 60947-2	
Category B	
Push-button	
Drawout	

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	66 kA 220/415 V AC 50/60 Hz 66 kA 440 V AC 50/60 Hz 66 kA 500/525 V AC 50/60 Hz 66 kA 660/690 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	66 kA 220/415 V AC 50/60 Hz 66 kA 440 V AC 50/60 Hz 66 kA 500/525 V AC 50/60 Hz 66 kA 660/690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	66 kA 0.5 s 66 kA 1 s 36 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	145 kA 220/415 V AC 50/60 Hz 145 kA 440 V AC 50/60 Hz 145 kA 500/525 V AC 50/60 Hz 145 kA 660/690 V AC 50/60 Hz

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sensor Rating	400 A
6	630 A
	800 A
	1000 A
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	150 W
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Mounting Support	Rails
	Base plate
Upside Connection	Front
	Rear
Downside Connection	Front
Downside Connection	Rear
Connection Pitch	4.53 in (115 mm)
Mechanical Durability	25000 cycles with periodic preventive maintenance
Electrical Durability	10000 cycles 440 V AC 50/60 Hz EN/IEC 60947-2
	10000 cycles 690 V AC 50/60 Hz EN/IEC 60947-2
	AC-23A 10000 cycles 440 V AC 50/60 Hz EN/IEC 60947-3
	AC-23A 10000 cycles 690 V AC 50/60 Hz EN/IEC 60947-3
	AC-3 6000 cycles 440/690 V AC 50/60 Hz EN/IEC 60947-3
Height	Drawout circuit breaker with chassis 17.28 in (439 mm)
neight	Drawout circuit breaker without chassis 17.20 in (439 min)
Width	Drawout circuit breaker with chassis 17.36 in (441 mm)
	Drawout circuit breaker without chassis 14.88 in (378 mm)
Depth	Drawout circuit breaker with chassis 15.87 in (403 mm)
	Drawout circuit breaker without chassis 10.07 in (400 mm)
Net Weight	198.42 lb(US) (90 kg)
Standards	EN/IEC 60947-1
	EN/IEC 60947-2
	EN/IEC 60947-2 Annex H
	IEC 61557-12
Product Certifications	CE
	IECEE CB Scheme

Environment

Ip Degree Of Protection	IP30 conforming to EN 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	06561.68 ft (02000 m) without derating 20005000 m with derating

Ordering and shipping details

Gtin

3606480808708

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	11.61 in (29.5 cm)
Package 1 Width	12.01 in (30.5 cm)
Package 1 Length	14.76 in (37.5 cm)
Package 1 Weight	103.70 lb(US) (47.036 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov