Product data sheet

Specifications





Circuit breaker frame, MasterPact MTZ2 12L1 drawout for MicroLogic X, 1250A, 150kA/415VAC (Icu), 3P

LV848261

Main

Range	MasterPacT	
Product Name	MasterPact MTZ2	
Device Short Name	MTZ2 12 L1	
Product Or Component Type	Circuit breaker	
Device Application	Power distribution protection	
Poles Description	3P	
Control Unit	Without control unit	
Product Compatibility	control unit MicroLogic 2.0 X control unit MicroLogic 5.0 X control unit MicroLogic 6.0 X control unit MicroLogic 7.0 X control unit MicroLogic 2.0 Xi control unit MicroLogic 5.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 6.0 Xi control unit MicroLogic 7.0 Xi	
Line Rated Current	1250 A 104 °F (40 °C)	
Performance Type	L1 150 kA 415 V AC	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz	
Suitability For Isolation	Yes EN/IEC 60947-2	
Selectivity Category	Category B	
Control Type	Push-button	
Mounting Mode	Drawout	

Complementary

[Icu] Rated Ultimate Short-Circuit Breaking Capacity	150 kA 220/415 V AC 50/60 Hz 150 kA 440 V AC 50/60 Hz 130 kA 500/525 V AC 50/60 Hz 100 kA 660/690 V AC 50/60 Hz
[Ics] Rated Service Breaking Capacity	150 kA 220/415 V AC 50/60 Hz 150 kA 440 V AC 50/60 Hz 130 kA 500/525 V AC 50/60 Hz 100 kA 660/690 V AC 50/60 Hz
[Icw] Rated Short-Time Withstand Current	30 kA 0.5 s 30 kA 1 s 30 kA 3 s
[Icm] Rated Short-Circuit Making Capacity	330 kA 220/415 V AC 50/60 Hz 330 kA 440 V AC 50/60 Hz 286 kA 500/525 V AC 50/60 Hz 220 kA 660/690 V AC 50/60 Hz
Integrated Instantaneous Protection (Din In Ka Peak)	7288 kA

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sensor Rating	630 A
	800 A
	1000 A
	1250 A
	1250 /1
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	12 kV
Power Dissipation In W	230 W
Maximum Breaking Time	10 ms
Maximum Closing Response Time	70 ms
Mounting Support	Rails
a	Base plate
	base plate
Upside Connection	Front
•	Rear
_	
Downside Connection	Front
	Rear
Connection Pitch	4.53 in (115 mm)
Manhanias I Dunchilitus	05000 1 111 1 1 1 1 1 1 1 1 1 1 1 1 1 1
Mechanical Durability	25000 cycles with periodic preventive maintenance
Electrical Durability	3000 cycles 690 V AC 50/60 Hz EN/IEC 60947-2
	3000 cycles 440 V AC 50/60 Hz EN/IEC 60947-2
	3000 Cycles 440 V AC 30/00 Hz EN/IEC 00947-2
Height	Drawout circuit breaker with chassis 17.28 in (439 mm)
· ·	Drawout circuit breaker without chassis 11.81 in (300 mm)
	Diamout Shoutt Stoution mittout of addition from the (Soo Hilling
Width	Drawout circuit breaker with chassis 17.36 in (441 mm)
	Drawout circuit breaker without chassis 14.88 in (378 mm)
Depth	Drawout circuit breaker with chassis 15.87 in (403 mm)
	Drawout circuit breaker without chassis 11.81 in (300 mm)
At a t Water to	(00.40.1/10) (00.1.)
Net Weight	198.42 lb(US) (90 kg)
Standards	EN/IEC 60947-1
	EN/IEC 60947-1 EN/IEC 60947-2
	EN/IEC 60947-2 EN/IEC 60947-2 Annex H
	IEC 61557-12
	ILO 01337-12
Product Certifications	CE
	IECEE CB Scheme

Environment

Ip Degree Of Protection	IP30 conforming to EN 60529
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Operating Altitude	06561.68 ft (02000 m) without derating 20005000 m with derating

Ordering and shipping details

Gtin 3606480806971

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.61 in (29.5 cm)

Package 1 Width	12.01 in (30.5 cm)
Package 1 Length	14.76 in (37.5 cm)
Package 1 Weight	109.53 lb(US) (49.682 kg)

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov