

Product data sheet

Specifications



contactor coil - LX1F - 300 V AC - 50/60 Hz

LX1FK300

! Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1FK
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F500
Control Circuit Type	AC 50/60 Hz
[Uc] Control Circuit Voltage	300 V AC 50/60 Hz
Average Resistance	72.6 Ohm inrush 68 °F (20 °C) 1917 Ohm holding 68 °F (20 °C)
Operating Time	100...170 ms opening 40...75 ms closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 131 °F (55 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational 0.85...1.1 Uc 50/60 Hz 131 °F (55 °C)) Drop-out 0.3...0.5 Uc 50/60 Hz 131 °F (55 °C))

Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
---------------------------------------	--------------------------

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
Gtin	3389118115255
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months