

Product data sheet

Specifications



TeSys Integral - coil - 36 V AC 60 Hz

LX1LD030

⚠ Discontinued on: Dec 23, 2020

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Coil
Range Compatibility	TeSys TeSys Integral contactor breaker
Device Short Name	LX1
Control Circuit Type	AC 60 Hz
[Uc] Control Circuit Voltage	36 V AC 60 Hz
Average Resistance	0.503 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	0.106 H

Complementary

Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at <131 °F (55 °C)) Drop-out: 0.25...0.7 Uc (at <131 °F (55 °C))
Inrush Power In Va	420...500 VA 60 Hz cos phi 0.55
Hold-In Power Consumption In Va	24...36 VA 60 Hz cos phi 0.28

Environment

Net Weight	0.66 lb(US) (0.3 kg)
------------	----------------------

Ordering and shipping details

Category	18402-WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
Gtin	3389110246438
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
<hr/>		