

Product data sheet

Specifications



standard digital input module - Modicon STB - 115 V AC - 2 I

STBDAI5260

 **Discontinued on:** Sep 9, 2009

 **Discontinued**

Main

Range Of Product	Modicon STB distributed I/O solution
Product Or Component Type	Standard digital input module
Discrete Input Number	2
Discrete Input Voltage	115 V
Discrete Input Voltage Type	AC

Complementary

Input Voltage Limits	0...20 V at state 0 74...132 V at state 1
Acceptable Input Voltage	132 V
Absolute Maximum Voltage	200 V 20 ms
Network Frequency	50/60 Hz
Network Frequency Limits	47...63 Hz
Current State 0 Guaranteed	<= 2 mA
Current State 1 Guaranteed	>= 4 mA
Discrete Input Logic	Positive or negative
Response Time	1.5 ms off-to-on 1.5 ms on-to-off
Protection Type	Input protection metal oxide varistor limited Power protection external fuse 0.5 A
Insulation Between Channels	1780 V for 1 minute
Insulation Between Channels And Logic Bus	1780 V for 1 minute
Cold Swapping	Yes
Hot Swapping	Yes for standard NIMs
Product Compatibility	Power distribution module STBPDT2100/2105 I/O base STBXBA2000
[Us] Rated Supply Voltage	115/230 V AC
Supply	Power distribution module
Current Consumption	45 mA 5 V DC logic bus
Marking	CE
Overvoltage Category	II

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Status Led	1 LED (Green) module status (RDY) 1 LED per channel (Green) channel status (IN1 to IN2) 1 LED (Red) module error (ERR)
Depth	2.56 in (65.1 mm)
Height	0.72 in (18.4 mm)
Width	4.92 in (125 mm)
Net Weight	0.14 lb(US) (0.065 kg)

Environment

Standards	EN/IEC 61131-2 type 1
Product Certifications	FM Class 1 Division 2 UL CSA
Pollution Degree	2 IEC 60664-1
Operating Altitude	<= 6561.68 ft (2000 m)
Ip Degree Of Protection	IP20 conforming to EN 61131-2 class 1
Ambient Air Temperature For Operation	32...140 °F (0...60 °C) without derating)
Ambient Air Temperature For Operation	32...140 °F without derating
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C) without derating
Ambient Air Temperature For Storage	-40...185 °F without derating
Relative Humidity	95 % 140 °F (60 °C) without condensation
Vibration Resistance	3 gn 58...150 Hz 35 x 7.5 mm symmetrical DIN rail 5 gn 58...150 Hz 35 x 15 mm symmetrical DIN rail +/-0.35 mm 10...58 Hz
Shock Resistance	30 gn 11 ms IEC 88 reference 2-27

Ordering and shipping details

Category	18215-ADVANTYS STB I/O
Discount Schedule	PC32
Gtin	00785901629382
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------