

Product data sheet

Specifications



TeSys F - contactor coil - LX0FJW - 395...439 V DC

LX2FJW37

⚠ Discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX2FJ
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F400
Control Circuit Type	DC wide range
[Uc] Control Circuit Voltage	395...439 V DC
Inductance Of Closed Circuit	0.44 H
Average Resistance	9.6 Ohm 68 °F (20 °C)
Mechanical Durability	10 Mcycles
Maximum Operating Rate	60 cyc/h 131 °F (55 °C)

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out 0.2...0.35 Uc 131 °F (55 °C)) Operational 0.85...1.1 Uc 131 °F (55 °C))
Inrush Power In W	290...860 W 68 °F (20 °C))
Hold-In Power Consumption In W	16...47 W 68 °F (20 °C)

Environment

Ambient Air Temperature For Operation	23...131 °F (-5...55 °C)
Net Weight	2.14 lb(US) (0.97 kg)

Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389118114821
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------