

# Product data sheet

Specifications



## coil LX4-D - 60 V DC

LX4D6ND

⚠ Discontinued on: Jul 12, 2021

⚠ Discontinued

### Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D6
[Uc] Control Circuit Voltage	60 V DC
Average Resistance	51.9 Ohm 68 °F (20 °C)
Inductance Of Closed Circuit	4.18 H
Product Compatibility	LC1D80...D95
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 140 °F (60 °C)

### Complementary

Range Compatibility	TeSys contactor
Coil Technology	Without built-in suppressor module

### Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Net Weight	0.62 lb(US) (0.28 kg)

### Ordering and shipping details

Category	18401-WORLD SERVICE PARTS(CTR ACCESS)
Discount Schedule	CP10
Gtin	3389110209785
Returnability	No

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	4.92 in (12.5 cm)
Package 1 Length	3.54 in (9 cm)
Package 1 Weight	15.94 oz (452 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.


**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a>
------------------------------	--