

Product data sheet

Specifications



Symmetra PX 90kW Scalable to 100kW, 208V with Startup, No Battery

SY90K100F-NB

Overview

Presentation A modular, high-efficiency 3-phase UPS that is scalable up to 100kW. Suitable for use in small to medium data centers and high density zones.

Lead Time Usually Ships within 3 Weeks

Main

Main Input Voltage 208 V 3 phase

Main Output Voltage 120 V
208 V
208 V 3 phase

Kw Rating 90000 W

Rated Power In Va 90000 VA

Output Connector Type Hard Wire 5-wire (3PH + N + G) 1

Battery Type External battery system

Provided Equipment Installation guide
Network Management Card
Start-Up Service
User Manual

Batteries & Runtime

Run Time [View Runtime Graph](#)

Efficiency [View Efficiency Graph](#)

Battery Slots Empty 0

Extendable Run Time 0

General

Number Of Power Module Free Slots 1

Number Of Power Module Filled Slots 9

Redundant Yes

Physical

Color Black

Height 79.17 in (201.1 cm)

Width 23.62 in (60 cm)

Depth 42.13 in (107 cm)

Net Weight 1200.42 lb(US) (544.5 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Usb Compatible	No
----------------	----

Input

Input Frequency	40 - 70 Hz
Efficiency At Full Load	177...239 V 208 V
Maximum Input Current Per Phase	332 A
Input Total Harmonic Distortion	Less than 5% for full load
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.99

Output

Max Configurable Power (Watts)	100000 W 100000 W
Harmonic Distortion	Less than 2%
Output Frequency (Sync To Mains)	57...63 Hz for 60 Hz nominal sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal not synced 50 Hz +/- 0.1 % for 50 Hz nominal not synced
Topology	Double Conversion Online
Wave Type	Sine wave
Output Voltage Tolerance	+/-1% static and +/- 5% at 100% load step
Output Voltage Thd	< 2% for 0 to 100% linear load and < 6% for full non-linear load
Bypass Type	Built-in Static Bypass
Maximum Configurable Power In Va	100000 VA
Transfer Time	2ms typical

Conformance

Standards	CSA C22.2 No.107.3-05 FCC Part 15 class A ISO 14001 ISO 9001 UL 1778
-----------	--

Environmental

Ambient Air Temperature For Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	5...104 °F (-15...40 °C)
Storage Relative Humidity	0...95 %
Storage Altitude	0...50000 ft (0.00...15240.00 m)
Acoustic Level	67 dBA
Nema Degree Of Protection	NEMA 1

Communications & Management

Free Slots	2
Control Panel	Multi-function LCD status and control console

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	84.25 in (214 cm)
Package 1 Width	47.64 in (121 cm)
Package 1 Length	33.39 in (84.8 cm)
Package 1 Weight	1381.86 lb(US) (626.8 kg)

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient

Resource performance

Energy Efficient Product

Eu Rohs Directive

Not compliant
