

Product data sheet

Specifications



Starter TeSys NEMA Sz3 3P 480VAC

T36EN13S7

Discontinued on: Nov 11, 2020

End-of-service on: Dec 31, 2020

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Starter
Range Of Product	TeSys N
Current Rating	90 A
Certifications	UL Listed CSA
Control Circuit Type	Common control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO
Horsepower Rating	25 HP 200 V AC 30 HP 230 V AC 50 HP 460 V AC 50 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	3
Control Circuit Voltage	500 V AC
Starter Type	Non reversing
Electrical Connection	Lugs ordered separately
Overload Type	Solid state MicroLogic class 10/20 30...90 A

Ordering and shipping details

Category	US10CP121199
Discount Schedule	0CP1
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	