

Product data sheet

Specifications



Miniature circuit breaker (MCB),
Multi9 C60H-DC, 2P, 6A, B curve,
5kA (UL1077), 6kA (IEC/EN
60947-2)

M9U11206

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 392.00 USD

Main

Range	Multi9
Product Name	Multi9 C60H-DC
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60H-DC
Device Application	Distribution
Poles Description	2P
Number Of Protected Poles	2
Line Rated Current	6 A 77 °F (25 °C) EN/IEC 60947-2
Network Type	DC
Trip Unit Technology	Thermal-magnetic
Curve Code	B
Breaking Capacity	20 kA Icu 220 V DC EN/IEC 60947-2 10 kA Icu 440 V DC EN/IEC 60947-2 6 kA Icu 500 V DC EN/IEC 60947-2 5 kA AIR 12...500 V DC UL 1077 20 kA Icu 220 V DC GB 14048.2 10 kA Icu 440 V DC GB 14048.2 6 kA Icu 500 V DC GB 14048.2
Utilisation Category	Category A EN/IEC 60947-2
Suitability For Isolation	Yes EN/IEC 60947-2
Standards	EN/IEC 60947-2 GB 14048.2 UL 1077
Product Certifications	IEC CCC UR

Complementary

[Ue] Rated Operational Voltage	220 V DC 440 V DC 500 V DC
Magnetic Tripping Limit	3...7 x In DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Ics] Rated Service Breaking Capacity	7.5 kA 75 % EN/IEC 60947-2 - 440 V DC 4.5 kA 75 % EN/IEC 60947-2 - 500 V DC 15 kA 75 % EN/IEC 60947-2 - 220 V DC 7.5 kA 75 % GB 14048.2 - 440 V DC 4.5 kA 75 % GB 14048.2 - 500 V DC 15 kA 75 % GB 14048.2 - 220 V DC
[Ui] Rated Insulation Voltage	500 V DC EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	6 kVEN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	3.19 in (81 mm)
Width	1.42 in (36 mm)
Depth	2.87 in (73 mm)
Net Weight	0.28 lb(US) (0.128 kg)
Color	Gray
Mechanical Durability	20000 cycles
Electrical Durability	3000 cycles 250 V DC L/R = 2 ms 6000 cycles 250 V DC
Provision For Padlocking	Padlockable
Connections - Terminals	Tunnel type terminal top or bottom) 0.00...0.04 in² (1...25 mm²) AWG 18...AWG 4) - rigid stranded Tunnel type terminal top or bottom) 0.00...0.02 in² (1...16 mm²) AWG 18...AWG 6) - flexible Tunnel type terminal top or bottom) 0.00...0.02 in² (1...16 mm²) AWG 18...AWG 6) - flexible with ferrule Tunnel type terminal top or bottom) - 2 0.00...0.02 in² (1...10 mm²) AWG 18...AWG 8) - rigid stranded Tunnel type terminal top or bottom) - 2 0.00...0.02 in² (1...10 mm²) AWG 18...AWG 8) - flexible Tunnel type terminal top or bottom) - 2 0.00...0.02 in² (1...10 mm²) AWG 18...AWG 8) - flexible with ferrule Tunnel type terminal top or bottom) - 3 0.00 in² (1 mm²) AWG 18) - flexible stranded
Wire Stripping Length	0.55 in (14 mm) for top or bottom connection
Tightening Torque	22.13 lbf.in (2.5 N.m) top or bottom
Earth-Leakage Protection	Without

Environment

Heat Dissipation	5.4 W 440 V - 6 A
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 EN/IEC 60947-2
Tropicalisation	2 IEC 60068-2 2 GB 14048.2
Relative Humidity	95 % 131 °F (55 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)

Ordering and shipping details

Category	US10DE200948
Discount Schedule	0DE2
Gtin	3606480741470
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	1.42 in (3.6 cm)
Package 1 Length	2.95 in (7.5 cm)
Package 1 Weight	7.87 oz (223.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	3.23 in (8.2 cm)
Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	8.86 in (22.5 cm)
Package 2 Weight	3.05 lb(US) (1.385 kg)
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	11.81 in (30.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	37.71 lb(US) (17.107 kg)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations