

Product data sheet

Specifications



Power quality meter, PowerLogic ION7400, Standard, integrated display, 512 MB, 256 s/c

METSEION7410

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8,928.36 USD

Main

Range	PowerLogic
Product Name	PowerLogic ION7400
Device Short Name	ION7410
Product Or Component Type	Power meter

Complementary

Power Quality Analysis	EN 50160 2010 compliance report IEEE 519 2014 compliance report IEC 61000-4-30 class S power quality measurement up to the 63rd harmonic harmonic distortion waveform capture voltage sag and swell detection programmability (logic and math functions) IEC 62586 power quality monitoring IEC 61000-4-15 disturbance direction detection rapid voltage change
------------------------	--

Device Application	Data aggregation Revenue billing WAGES metering Power monitoring
--------------------	---

Type Of Measurement	Current Voltage Frequency Active and reactive power total Apparent power total Power factor total Active and reactive power per phase, rms Apparent power per phase, rms Power factor per phase, rms Active and reactive energy Apparent energy
---------------------	---

Supply Voltage	20...60 V DC +/- 10 %
----------------	-----------------------

Network Frequency	50 Hz 60 Hz
-------------------	----------------

Line Rated Current	10 A 1 A 5 A
--------------------	--------------------

Poles Description	1P + N 3P + N 3P
-------------------	------------------------

Power Consumption In W	17 W
------------------------	------

Display Type	Colour TFT LCD
--------------	----------------

Display Resolution	320 x 240 pixels QVGA
--------------------	-----------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sampling Rate	256 samples/cycle
Measurement Current	50...10000 mA
Analogue Input Type	Voltage (impedance 5 MΩ) Current (impedance 0.3 mΩ)
Measurement Voltage	57...400 V AC 42...69 Hz between phase and neutral 100...690 V AC 42...69 Hz between phases
Frequency Measurement Range	42...69 Hz
Number Of Inputs	3 digital 30 V AC 3 digital 60 V DC
Measurement Accuracy	Current +/- 0.1 % Voltage +/- 0.1 % Active energy +/- 0.2 %
Accuracy Class	Class 0.2S active energy IEC 62053-22 Class 0.2 active energy ANSI C12.20 Class 0.2 active power IEC 61557-12 Class 0.5S reactive energy IEC 62053-24 Class 0.5 power factor IEC 61557-12 Class 0.2 voltage IEC 61557-12 Class 0.2 current IEC 61557-12 Class 0.2 frequency IEC 61557-12 Class 0.2 active energy IEC 61557-12
Number Of Outputs	1 pulse
Information Displayed	Voltage Current Frequency Power Energy consumption Harmonic distortion
Communication Port Protocol	Modbus RTU 115 kbauds - 2-wire ION 115 kbauds - 2-wire DNP3 IEC 61850 Modbus TCP/IP Ethernet Modbus TCP/IP daisy chain 10/100 Mbit/s RSTP 801.1d 2004 Ansi C12.19 DLMS
Communication Port Support	ETHERNET Screw terminal block RS485 Optical probe fiber optic Mini B USB USB
Communication Network Type	IPv6 (internet protocol)
Data Recording	Data logs Sag and swell logs Waveform logs Trending/forecasting Sequence of event recording GPS synchronisation Harmonics logs Time stamping Alarm logs Event logs Min/max of instantaneous values 50 data recorders
Memory Capacity	512 MB
Web Services	Customizable home page File upload/download via FTP File upload/download via SFTP Web server Alarm notification by e-mail Viewing of captured waveform (FTP) Viewing of captured waveform (web) HTTPS server

Communication Service	SNMP SMTP e-mail notification RSTP support DHCP NTP time synchronization PTP time synchronization
Cybersecurity	Enable/disable communication ports Port hardening Syslog protocol support Password protection Robust security logs
Mounting Mode	Flush-mounted
Mounting Support	Framework
Type Of Installation	Indoor installation
Installation Category	III
Safety Construction	III400...690 V conforming to IEC 61010-1:ed. 3 III400...690 V conforming to EN 61010-1:ed. 3 III347...600 V conforming to UL 61010-1:ed. 3 III347...600 V conforming to CSA C22.2 No 61010-1:ed. 3
Standards	IEC 61557-12 IEC 61326-1 IEC 62052-11 IEC 62053-24 IEC 62053-22 IEEE 1588 IEC 62586
Product Certifications	CE CULus N998
Width	3.86 in (98 mm)
Depth	3.09 in (78.5 mm)
Height	4.41 in (112 mm)
Net Weight	24.90 oz (706 g)

Environment

Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Immunity to impulse waves conforming to IEC 61000-4-12 Conducted and radiated emissions conforming to EN 55022 Conducted and radiated emissions conforming to EN 55011 Conducted and radiated emissions conforming to FCC part 15 Conducted and radiated emissions conforming to ICES-003 Conducted RF disturbances (2...150 Hz) conforming to CLC/TR 50579 Surge withstand conforming to IEEE C37.90.1
Ip Degree Of Protection	IP54 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative Humidity	5...95 %
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Operating Altitude	9842.52 ft (3000 m)

Ordering and shipping details

Category	US10PM109753
Discount Schedule	0PM1
Gtin	3606481384577
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.51 in (14.0 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	7.28 in (18.5 cm)
Package 1 Weight	2.27 lb(US) (1.03 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov