Product data sheet

Specification

Main





Multi9 - C60 UL1077 - MCB - 2P - 3 A - C Curve - 480Y/277 V - 5 kA

MG24444

Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

| Range | Multi9 |
|---------------------------|---------------------------|
| Product Or Component Type | Miniature circuit-breaker |
| Product Name | Multi9 C60 |
| Device Short Name | C60 UL1077 |
| Device Application | Distribution |
| Number Of Protected Poles | 2 |
| Line Rated Current | 3 A 77 °F (25 °C) |
| Network Type | DC AC |
| Trip Unit Technology | Thermal-magnetic |
| Suitability For Isolation | Yes EN/IEC 60947-2 |

Complementary

| o o in promontary | |
|--|-------------------------|
| System Voltage | 240 V |
| | 415 V |
| | 440 V |
| | 125 V |
| Mounting Mode | Clip-on |
| Poles Description | 2P |
| Interrupt Rating | 20 kA |
| | 10 kA |
| | 6 kA |
| | 5 kA |
| Network Frequency | 50/60 Hz |
| Curve Code | С |
| Magnetic Tripping Limit | 8.5 x In +/- 20 % AC |
| | 12 x ln +/- 20 % DC |
| Limitation Class | 3 EN/IEC 60947-2 |
| [Ui] Rated Insulation Voltage | 500 V AC EN/IEC 60947-2 |
| [Uimp] Rated Impulse Withstand Voltage | 6 kVEN/IEC 60947-2 |
| Contact Position Indicator | Yes |
| Control Type | Toggle |
| Local Signalling | ON/OFF indication |
| Mounting Support | DIN rail |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| 9 Mm Pitches | 4 |
|--------------------------|---|
| Height | 3.19 in (81 mm) |
| Width | 1.42 in (36 mm) |
| Depth | 2.87 in (73 mm) |
| Net Weight | 0.49 lb(US) (0.22 kg) |
| Color | Gray |
| Mechanical Durability | 20000 cycles |
| Electrical Durability | 10000 cycles |
| Provision For Padlocking | Padlockable |
| Connections - Terminals | Tunnel type terminal top or bottom) 0.000.04 in² (2.525 mm²) AWG 14AWG 4) - rigid |
| Wire Stripping Length | 0.55 in (14 mm) for top or bottom connection |
| Tightening Torque | 22.13 lbf.in (2.5 N.m) top or bottom |

Environment

| Standards | GB 14048.2 EN/IEC 60947-2 UL 1077 CSA C22.2 No 235 |
|---------------------------------------|---|
| Product Certifications | UR CSA CCC IEC |
| Ip Degree Of Protection | IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529 |
| Pollution Degree | 3 EN/IEC 60947-2 |
| Overvoltage Category | IV |
| Tropicalisation | 2 IEC 60068-1 |
| Relative Humidity | 95 % 131 °F (55 °C) |
| Operating Altitude | 6561.68 ft (2000 m) |
| Ambient Air Temperature For Operation | -22158 °F (-3070 °C) |
| Ambient Air Temperature For Storage | -40176 °F (-4080 °C) |

Ordering and shipping details

| Category | US10DE200908 |
|-------------------|----------------|
| Discount Schedule | 0DE2 |
| Gtin | 00785901346319 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.40 in (3.556 cm) |
| Package 1 Width | 3.00 in (7.62 cm) |

| Package 1 Length | 3.20 in (8.128 cm) |
|------------------|---------------------|
| Package 1 Weight | 8.32 oz (235.868 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

| ② | Mercury Free | |
|----------|----------------------------|-----|
| ⊘ | Rohs Exemption Information | Yes |
| ⊘ | Halogen Free Product | |

Certifications & Standards

| Eu Rohs Directive | Compliant |
|-----------------------|--|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Product out of China RoHS scope. Substance declaration for your information. |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |