Product data sheet

Specification





Pendant control station, Harmony XAC, plastic, yellow, pistol grip, 2 push buttons with 2NO, 1 emergency stop NC

XACA2073

Product availability: Stock - Normally stocked in distribution facility

Price*: 246.00 USD

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

Control Station Type	trol Station Type Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical Circuit Type	Control circuit	
Enclosure Type	Complete ready for use	
Control Station Application	Control of 2-speed hoist motor	
Control Station Composition	2 push-buttons + 1 emergency stop	
Control Button Type	Stop push-button Ø 30 mm 1 NC latching First push-button 2 NO (2 step) raise, slow-fast Second push-button 2 NO (2 step) lower, slow-fast	
Product Compatibility	ZB2BE102 for emergency stop ZB2BE101 + ZB2BE201 for each direction	
Mechanical Interlocking	With mechanical interlocking	
Control Station Colour	Yellow	
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm ² with or without cable end Screw clamp terminals, 2 x 1.5 mm ² with or without cable end	
Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508 EN/IEC 60204-32	
Product Certifications	UL CSA	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK08 conforming to EN 50102	
Mechanical Durability	1000000 cycles	
Cable Entry	Rubber sleeve with stepped entry 0.280.59 in (715 mm)	
Contact Code Designation	de Designation A600 AC-15, Ue = 240 V, Ie = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, Ie = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, Ie = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, Ie = 0.1 A IEC 60947-5-1 appendix A	
[Ithe] Conventional Enclosed Thermal Current	10 A	
[Ui] Rated Insulation Voltage	Voltage 600 V 3)IEC 60947-1	
Uimp] Rated Impulse Withstand 6 kV IEC 60947-1 /oltage		
Contact Operation	Staggered Slow-break	
Maximum Resistance Across Terminals	25 MOhm	
Operating Force	1315 N	
Short-Circuit Protection	10 A fuse protection cartridge gG	
Rated Operational Power In W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C	
Terminals Description Iso N°1	(23-24)NO_CL (13-14)NO	
Terminals Description Iso N°2	(11-12)NC	
Terminal Identifier	(11-12)NC (13-14)NO	
Net Weight	0.79 lb(US) (0.36 kg)	

Ordering and shipping details

Category	US10CS222473
Discount Schedule	0CS2
Gtin	3389110558890
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.03 in (7.700 cm)
Package 1 Width	4.65 in (11.800 cm)
Package 1 Length	13.43 in (34.100 cm)
Package 1 Weight	12.80 oz (363.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	15

Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	13.08 lb(US) (5.935 kg)	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	120	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	23.62 in (60.000 cm)	
Package 3 Length	31.50 in (80.000 cm)	
Package 3 Weight	128.14 lb(US) (58.124 kg)	

Contractual warranty

Warranty 18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov