Product data sheet

Specifications





Pendant control station, Harmony XAC, plastic, yellow, pistol grip, 2 booted push buttons with 2NO

XACA217

Product availability: Stock - Normally stocked in distribution facility

Price*: 270.00 USD

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACA pistol grip

Complementary

· · · · · · · · · · · · · · · · · ·		
Control Station Type	Double insulated	
Enclosure Material	Polypropylene	
Control Type	Intuitive	
Electrical Circuit Type	Control circuit	
Enclosure Type	Complete ready for use	
Control Station Application	Control of 2-speed hoist motor	
Control Station Composition	2 booted push-buttons	
Control Button Type	First push-button 2 NO (2 step) raise, slow-fast Second push-button 2 NO (2 step) lower, slow-fast	
Product Compatibility	ZB2BE101 + ZB2BE201 for each direction	
Mechanical Interlocking	erlocking With mechanical interlocking	
Control Station Colour	ur Yellow	
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm^2 with or without cable end Screw clamp terminals, $2 \times 1.5 \text{ mm}^2$ with or without cable end	
Standards	IEC 60204-32 UL 508 IEC 60947-5-1 CSA C22.2 No 14	
Product Certifications	CSA UL	
Protective Treatment	тн	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6	
Shock Resistance	100 gn IEC 60068-2-27	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ik Degree Of Protection	tion IK08 conforming to IEC 62262		
Mechanical Durability	1000000 cycles		
Cable Entry	Rubber sleeve with stepped entry 0.280.59 in (715 mm)		
Contact Code Designation	A600 AC-15, Ue = 240 V, le = 3 A IEC 60947-5-1 appendix A A600 AC-15, Ue = 600 V, le = 1.2 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 250 V, le = 0.27 A IEC 60947-5-1 appendix A Q600 DC-13, Ue = 600 V, le = 0.1 A IEC 60947-5-1 appendix A		
[Ithe] Conventional Enclosed Thermal Current	10 A		
[Ui] Rated Insulation Voltage	600 V 3)IEC 60947-1		
[Uimp] Rated Impulse Withstand Voltage	stand 6 kV IEC 60947-1		
Contact Operation	Slow-break Staggered		
Maximum Resistance Across Terminals	25 MOhm		
Operating Force	1315 N		
Short-Circuit Protection	10 A fuse protection cartridge gG		
Rated Operational Power In W	40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C 48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C 65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C		
Terminals Description Iso N°1	(23-24)NO_CL (13-14)NO		
Terminal Identifier	(13-14)NO (11-12)NC		
Net Weight	0.71 lb(US) (0.32 kg)		

Ordering and shipping details

Category	US1000T18407
Discount Schedule	000T
Gtin	3389110644852
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.6 cm)
Package 1 Width	3.54 in (9.0 cm)
Package 1 Length	11.81 in (30.0 cm)
Package 1 Weight	10.48 oz (297.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)

Package 2 Weight

10.45 lb(US) (4.741 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

Dimensions Drawings

Dimensions




(1) Internal Ø

Product data sheet

XACA217

Connections and Schema

Control of 2-Speed Reversing Motor




XACA217

Performance Curves

Rated Operational Power

AC Supply 50/60 Hz Inductive Circuit

Operating rate: 3600 operating cycles/hour. Load factor: 0.5. Millions of operating cycles, AC-15 utilization category



Ithe Thermal current

(A) Current

DC Supply

Operating rate: 3600 operating cycles/hour. Load factor: 0.5.

Power broken in W for 1 million operating cycles, DC-13 utilization category

Voltage	V	24	48	120
Inductive circuit	w	65	48	40