

Product data sheet

Specifications



pendant station XAC-D - 1 rocker lever 1 Emergency stop

XACD22P2121

! Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACD

Complementary

Control Station Type	Double insulated
Enclosure Material	Polypropylene
Control Type	Intuitive
Electrical Circuit Type	Power circuit
Enclosure Type	Complete ready for use
Control Station Application	Control of single speed hoist motor
Motor Starter Type	Reversing
Control Station Composition	1 2-directional button + 1 emergency stop
Control Button Type	Stop push-button Ø 30 mm 3 NC latching First direction button 1 NO (brake) 2-pole raise, slow Second direction button 1 NO (brake) 2-pole lower, slow
Product Compatibility	XEDS2121 for reversing operation XENT1991 for emergency stop
Mechanical Interlocking	With mechanical interlocking
Control Station Colour	Yellow
Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Standards	IEC 60947-5-1 IEC 60204-32 CSA C22.2 No 14 UL 508
Protective Treatment	TH
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK08 conforming to IEC 62262
Mechanical Durability	3000000 cycles
Cable Entry	Rubber sleeve with stepped entry 0.28...0.71 in (7...18 mm)
[Ithe] Conventional Enclosed Thermal Current	10 A XENT.... 16 A XEDS....
[Ui] Rated Insulation Voltage	500 V 3)IEC 60947-1 Emergency stop contact 400 V 3)
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1 4 kV emergency stop contact
Contact Operation	Snap action
Operating Force	28 N
Short-Circuit Protection	6 A fuse protection cartridge aM
Rated Operational Power In W	1100 W AC-3 400 V IEC 60947-3 appendix A 1100 W AC-4 400 V IEC 60947-3 appendix A 3000 W AC-23B 400 V
Electrical Durability	1000000 cycles AC-3, 1100 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A 1000000 cycles AC-4, 1100 W 400 V 10 cyc/mn 0.4 IEC 60947-3 appendix A
Terminals Description Iso N°1	(15-16)NO (1-2)P (13-14)NO (3-4)P (7-8)P (5-6)P
Terminals Description Iso N°2	(31-32)NC (11-12)NC (21-22)NC
Terminal Identifier	(11-12)NC (13-14)NO
Net Weight	0.90 lb(US) (0.41 kg)

Ordering and shipping details

Category	22473-PUSHBUTTON, PENDANTS
Discount Schedule	CS2
Gtin	3389110656015
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	4.80 in (12.2 cm)
Package 1 Length	12.40 in (31.5 cm)
Package 1 Weight	20.39 oz (578.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	3
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	4.56 lb(US) (2.068 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov