Product data sheet

Specifications





() Discontinued - Service only

servo motor MH3 070 1,4Nm,no key,single16 lines,no brake,IP65/ IP67,6kRPM

MH30701P06F2200

() Discontinued on: Sep 30, 2023

() To be end-of-service on: Mar 31, 2025

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Compatibility	PacDrive 3	
Product Or Component Type	AC servo motors	
Device Short Name	MH3	

Complementary

Complementary	
Maximum Mechanical Speed	8000 rpm
[Us] Rated Supply Voltage	115480 V
Phase	Three phase
Continuous Stall Current	1.78 A
Continuous Stall Torque	12.39 lbf.in (1.4 N.m), 115480 V, three phase
Continuous Power	930 W
Peak Stall Torque	37.17 lbf.in (4.2 N.m), 115480 V, three phase
Nominal Output Power	0.18 W, 115 V 0.42 W, 230 V 0.75 W, 400 V 0.93 W, 480 V
Nominal Torque	12.21 lbf.in (1.38 N.m) LXM52 1.75 mA, 115 V, 1 phase 11.86 lbf.in (1.34 N.m) LXM52 1.75 mA, 230 V, 1 phase 11.51 lbf.in (1.3 N.m) LXM52 1.72 mA, 400 V, 3 phase 11.24 lbf.in (1.27 N.m) LXM52 1.7 mA, 480 V, 3 phase 12.21 lbf.in (1.38 N.m) LXM62 1.75 mA, 115 V, 1 phase 11.86 lbf.in (1.34 N.m) LXM62 1.75 mA, 230 V, 1 phase 11.51 lbf.in (1.3 N.m) LXM62 1.72 mA, 400 V, 3 phase 11.24 lbf.in (1.27 N.m) LXM62 1.7 mA, 480 V, 3 phase
Nominal Speed	1250 rpm LXM52 1.75 mA, 115 V, 1 phase 3000 rpm LXM52 1.75 mA, 230 V, 1 phase 5500 rpm LXM52 1.72 mA, 400 V, 3 phase 7000 rpm LXM52 1.7 mA, 480 V, 3 phase 1250 rpm LXM62 1.75 mA, 115 V, 1 phase 3000 rpm LXM62 1.75 mA, 230 V, 1 phase 5500 rpm LXM62 1.72 mA, 400 V, 3 phase 7000 rpm LXM62 1.7 mA, 480 V, 3 phase
Maximum Current Irms	5.97 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	0.43 in (11 mm)
Shaft Length	0.91 in (23 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP65 standard
Encoder Type	Single turn SinCos Hiperface
Speed Feedback Resolution	16 periods
Holding Brake	With
Holding Torque	26.55 lbf.in (3 N.m)
Mounting Support	International standard flange
Motor Flange Size	2.76 in (70 mm)
Electrical Connection	Rotatable right-angled connectors
Torque Constant	0.79 N.m/A 248 °F (120 °C)
Back Emf Constant	50.72 V/krpm
Number Of Motor Poles	10
Rotor Inertia	0.7 kg.cm ²
Stator Resistance	8.28 Ohm
Stator Inductance	23.4 mH
Stator Electrical Time Constant	2.8 ms
Maximum Radial Force Fr	660 N 1000 rpm 520 N 2000 rpm 460 N 3000 rpm 410 N 4000 rpm 380 N 5000 rpm 360 N 6000 rpm
Brake Pull-In Power	7 W
Type Of Cooling	Natural convection
Length	6.34 in (161 mm)
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	5.73 lb(US) (2.6 kg)

Ordering and shipping details

Category	US1PC5218359	
Discount Schedule	PC52	
Gtin	3606485394886	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	7.48 in (19.0 cm)

Package 1 Length

15.55 in (39.5 cm)

Package 1 Weight

4.63 lb(US) (2.1 kg)

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov