# Product data sheet

Specifications





### servo motor MH3 100 3,3Nm,no key,single,no brake,IP65/ IP67,4kRPM

MH31001P01A2200

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 1,809.30 USD

### Main

Range Compatibility	PacDrive 3	
Product Or Component Type	AC servo motors	
Device Short Name	MH3	

### Complementary

Complementary	
Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115480 V
Phase	Three phase
Continuous Stall Current	3.15 A
Continuous Stall Torque	30.09 lbf.in (3.4 N.m), 115480 V, three phase
Continuous Power	1520 W
Peak Stall Torque	95.59 lbf.in (10.8 N.m), 115480 V, three phase
Nominal Output Power	0.35 W, 115 V 0.67 W, 230 V 1.26 W, 400 V 1.52 W, 480 V
Nominal Torque	29.21 lbf.in (3.3 N.m) LXM52 3.07 mA, 115 V, 1 phase 28.32 lbf.in (3.2 N.m) LXM52 2.99 mA, 230 V, 1 phase 26.55 lbf.in (3 N.m) LXM52 2.83 mA, 400 V, 3 phase 25.67 lbf.in (2.9 N.m) LXM52 2.75 mA, 480 V, 3 phase 29.21 lbf.in (3.3 N.m) LXM62 3.07 mA, 115 V, 1 phase 28.32 lbf.in (3.2 N.m) LXM62 2.99 mA, 230 V, 1 phase 26.55 lbf.in (3 N.m) LXM62 2.83 mA, 400 V, 3 phase 25.67 lbf.in (2.9 N.m) LXM62 2.75 mA, 480 V, 3 phase
Nominal Speed	1000 rpm LXM52 3.07 mA, 115 V, 1 phase 2000 rpm LXM52 2.99 mA, 230 V, 1 phase 4000 rpm LXM52 2.83 mA, 400 V, 3 phase 5000 rpm LXM52 2.75 mA, 480 V, 3 phase 1000 rpm LXM62 3.07 mA, 115 V, 1 phase 2000 rpm LXM62 2.99 mA, 230 V, 1 phase 4000 rpm LXM62 2.83 mA, 400 V, 3 phase 5000 rpm LXM62 2.75 mA, 480 V, 3 phase
Maximum Current Irms	10.68 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Ip Degree Of Protection	IP65 standard

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Encoder Type	Single turn SinCos Hiperface	
Speed Feedback Resolution	128 periods	
Holding Brake	Without	
Mounting Support	International standard flange	
Motor Flange Size	3.94 in (100 mm)	
Electrical Connection	Rotatable right-angled connectors	
Torque Constant	1.09 N.m/A 248 °F (120 °C)	
Back Emf Constant	70.3 V/krpm	
Number Of Motor Poles	10	
Rotor Inertia	3.19 kg.cm <sup>2</sup>	
Stator Resistance	4.12 Ohm	
Stator Inductance	14.9 mH	
Stator Electrical Time Constant	4.5 ms	
Maximum Radial Force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm	
Maximum Radial Force Fr Type Of Cooling	720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm	
	720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm	
Type Of Cooling	720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm Natural convection	
Type Of Cooling Length	720 N 2000 rpm     630 N 3000 rpm     570 N 4000 rpm     530 N 5000 rpm     Natural convection     5.06 in (128.6 mm)	
Type Of Cooling Length Centring Collar Diameter	720 N 2000 rpm     630 N 3000 rpm     570 N 4000 rpm     530 N 5000 rpm     Natural convection     5.06 in (128.6 mm)     3.74 in (95 mm)	
Type Of Cooling Length Centring Collar Diameter Centring Collar Depth	720 N 2000 rpm     630 N 3000 rpm     570 N 4000 rpm     530 N 5000 rpm     Natural convection     5.06 in (128.6 mm)     3.74 in (95 mm)     0.14 in (3.5 mm)	
Type Of Cooling Length Centring Collar Diameter Centring Collar Depth Number Of Mounting Holes	720 N 2000 rpm     630 N 3000 rpm     570 N 4000 rpm     530 N 5000 rpm     Natural convection     5.06 in (128.6 mm)     3.74 in (95 mm)     0.14 in (3.5 mm)     4	

## Ordering and shipping details

Category	US1PC5218359	
Discount Schedule	PC52	
Gtin	3606485395746	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	7.80 lb(US) (3.54 kg)

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov