Product data sheet

Specifications





servo motor MH3 100 8Nm,no key,single,brake,IP65/IP67,4kRPM

MH31003P01F2200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,100.54 USD

Main

Range Compatibility	PacDrive 3
Product Or Component Type	AC servo motors
Device Short Name	MH3

Complementary

•	
Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	115480 V
Phase	Three phase
Continuous Stall Current	7.69 A
Continuous Stall Torque	79.66 lbf.in (9 N.m), 115480 V, three phase
Continuous Power	3270 W
Peak Stall Torque	238.97 lbf.in (27 N.m), 115480 V, three phase
Nominal Output Power	0.88 W, 115 V 2 W, 230 V 2.85 W, 400 V 3.27 W, 480 V
Nominal Torque	74.79 lbf.in (8.45 N.m) LXM52 7.3 mA, 115 V, 1 phase 67.53 lbf.in (7.63 N.m) LXM52 6.7 mA, 230 V, 1 phase 60.18 lbf.in (6.8 N.m) LXM52 6.07 mA, 400 V, 3 phase 55.32 lbf.in (6.25 N.m) LXM52 5.64 mA, 480 V, 3 phase 74.79 lbf.in (8.45 N.m) LXM62 7.3 mA, 115 V, 1 phase 67.53 lbf.in (7.63 N.m) LXM62 6.7 mA, 230 V, 1 phase 60.18 lbf.in (6.8 N.m) LXM62 6.07 mA, 400 V, 3 phase 55.32 lbf.in (6.25 N.m) LXM62 5.64 mA, 480 V, 3 phase
Nominal Speed	1000 rpm LXM52 7.3 mA, 115 V, 1 phase 2500 rpm LXM52 6.7 mA, 230 V, 1 phase 4000 rpm LXM52 6.07 mA, 400 V, 3 phase 5000 rpm LXM52 5.64 mA, 480 V, 3 phase 1000 rpm LXM62 7.3 mA, 115 V, 1 phase 2500 rpm LXM62 6.7 mA, 230 V, 1 phase 4000 rpm LXM62 6.07 mA, 400 V, 3 phase 5000 rpm LXM62 5.64 mA, 480 V, 3 phase
Maximum Current Irms	26.71 A
Shaft End	Smooth shaft
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Ip Degree Of Protection	IP65 standard
Encoder Type	Single turn SinCos Hiperface

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Speed Feedback Resolution	128 periods
Holding Brake	With
Holding Torque	79.66 lbf.in (9 N.m)
Mounting Support	International standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Rotatable right-angled connectors
Torque Constant	1.17 N.m/A 248 °F (120 °C)
Back Emf Constant	77.95 V/krpm
Number Of Motor Poles	10
Rotor Inertia	10.3 kg.cm ²
Stator Resistance	1.08 Ohm
Stator Inductance	5.23 mH
Stator Electrical Time Constant	6.3 ms
Maximum Radial Force Fr	1050 N 1000 rpm 830 N 2000 rpm 730 N 3000 rpm 660 N 4000 rpm 610 N 5000 rpm
Brake Pull-In Power	18 W
Type Of Cooling	Natural convection
Length	9.22 in (234.3 mm)
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Net Weight	17.97 lb(US) (8.15 kg)

Ordering and shipping details

_	
Category	US1PC5218359
Discount Schedule	PC52
Gtin	3606485396408
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.27 in (21.0 cm)
Package 1 Width	7.09 in (18.0 cm)
Package 1 Length	14.02 in (35.6 cm)
Package 1 Weight	16.42 lb(US) (7.45 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov