Product data sheet

Specifications





Cylindrical barrel MICHELIN lock 8133 without key

NSYINICHEL8131

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 547.36 USD

Main

Range	Spacial
Accessory / Separate Part Category	Locking accessory
Product Or Component Type	Cylindrical barrel
Application	Multi-purpose
Mounting Support	Handle
Product Compatibility	SF, SM and SD enclosures
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	1 cylindrical barrel

Complementary

Quantity Per Set	Set of 1	
Type Of Keylock	MICHELIN	
Key Number	8133	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480064906
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	1.98 oz (56.0 g)

Contractual warranty

Warranty

18 months

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations