Product data sheet

Specifications





Illuminated push button, Harmony XB5, plastic, red flush, 22mm, universal LED, plain lens, 1NO + 1NC, 110...120V AC

XB5AW34G5

Product availability: Stock - Normally stocked in distribution facility

Important message: Viktig information: en förändring i utseendet kan observeras på produkten, men detta påverkar inte dess användning i termer av funktion och säkerhet. Detta gör den kompatibel med våra Universal LED-block

Price*: 119.00 USD

Main

mann	
Range Of Product	Harmony XB5
Product Or Component Type	Illuminated push-button
Device Short Name	XB5
Bezel Material	Dark grey plastic
Fixing Collar Material	Plastic
Head Type	Standard
Mounting Diameter	0.89 in (22.5 mm)
Sale Per Indivisible Quantity	1
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Operator Profile	Red flush, unmarked
Operator Additional Information	With plain lens
Contacts Type And Composition	1 NO + 1 NC
Contact Operation	Slow-break
Connections - Terminals	Screw clamp terminals, <= 2 x 1.5 mm ² with cable end IEC 60947-1 Screw clamp terminals, 1 x 0.222 x 2.5 mm ² without cable end IEC 60947-1
Light Source	Universal LED
Bulb Base	Integral LED
[Us] Rated Supply Voltage	110120 V AC 50/60 Hz
Cap/Operator Or Lens Colour	Red

Complementary

Height	1.65 in (42 mm)
Width	1.18 in (30 mm)
Depth	2.24 in (57 mm)
Terminals Description Iso N°1	(13-14)NO (21-22)NC

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Net Weight	0.12 lb(US) (0.056 kg)					
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m					
Contacts Usage	Standard contacts					
Positive Opening	With IEC 60947-5-1 appendix K					
Operating Travel	0.06 in (1.5 mm) NC changing electrical state) 0.10 in (2.6 mm) NO changing electrical state) 0.17 in (4.3 mm) total travel)					
Operating Force	3.5 N NC changing electrical state 3.8 N					
Mechanical Durability	1000000 cycles					
Tightening Torque	7.0810.62 lbf.in (0.81.2 N.m) IEC 60947-1					
Shape Of Screw Head	Cross Philips no 1 Cross pozidriv No 1 Slotted flat Ø 4 mm Slotted flat Ø 5.5 mm					
Contacts Material	Silver alloy (Ag/Ni)					
Short-Circuit Protection	10 A cartridge fuse gG IEC 60947-5-1					
[Ith] Conventional Free Air Thermal Current	10 A IEC 60947-5-1					
[Ui] Rated Insulation Voltage	600 V 3)IEC 60947-1					
[Uimp] Rated Impulse Withstand Voltage	6 kV IEC 60947-1					
[Ie] Rated Operational Current	3 A 240 V, AC-15, A600 IEC 60947-5-1 6 A 120 V, AC-15, A600 IEC 60947-5-1 0.1 A 600 V, DC-13, Q600 IEC 60947-5-1 0.27 A 250 V, DC-13, Q600 IEC 60947-5-1 0.55 A 125 V, DC-13, Q600 IEC 60947-5-1 1.2 A 600 V, AC-15, A600 IEC 60947-5-1					
Electrical Durability	1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 3 A 120 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, AC-15, 4 A 24 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.2 A 110 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-13, 0.5 A 24 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C					
Electrical Reliability	Λ < 10exp(-6) 5 V, 1 mA in clean environment IEC 60947-5-4 Λ < 10exp(-8) 17 V, 5 mA in clean environment IEC 60947-5-4					
Signalling Type	Steady					
Supply Voltage Limits	100132 V AC					
Current Consumption	14 mA					
Service Life	100000 h at rated voltage and 25 °C					
Surge Withstand	1 kV IEC 61000-4-5					
Device Presentation	Complete product					

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class II IEC 60536
Ip Degree Of Protection	IP66 IEC 60529 IP69 IP69K IP67

Nema Degree Of Protection	NEMA 13		
	NEMA 4X		
Ik Degree Of Protection	IK05 conforming to IEC 50102		
Standards	UL 508		
	CSA C22.2 No 14 IEC 60947-1		
	JIS C8201-5-1		
	IEC 60947-5-4		
	IEC 60947-5-1		
	JIS C8201-1		
Product Certifications	BV		
	CSA		
	UL Listed		
	LROS (Lloyds register of shipping)		
	GL		
	DNV		
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6		
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27		
	50 gn 11 ms) half sine wave acceleration IEC 60068-2-27		
Resistance To Fast Transients	2 kV IEC 61000-4-4		
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3		
Resistance To Electrostatic	6 kV on contact (on metal parts) IEC 61000-4-2		
Discharge	8 kV in free air (in insulating parts) IEC 61000-4-2		
Electromagnetic Emission	Class B IEC 55011		

Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
Gtin	3389110904130
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.26 in (3.200 cm)
Package 1 Width	2.05 in (5.200 cm)
Package 1 Length	3.31 in (8.400 cm)
Package 1 Weight	1.94 oz (55.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.46 in (8.800 cm)
Package 2 Width	1.34 in (3.400 cm)
Package 2 Length	10.43 in (26.500 cm)
Package 2 Weight	9.84 oz (279.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	50
Package 3 Height	5.91 in (15.000 cm)

Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	6.72 lb(US) (3.046 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
 Yes


Certifications & Standards

Reach Regulation	REACh Declaration Pro-active compliance (Product out of EU RoHS legal scope)				
Eu Rohs Directive					
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Weee Circularity Profile					

Product data sheet

Dimensions Drawings

Dimensions




e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.(1) Additional row of contacts or double contact.

Product data sheet

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board




(1) Diameter on finished panel or support

(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. (3) \emptyset 22.5 mm recommended (\emptyset 22.3 $_0^{+0.4}$) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0^{+0.016}$)

				0 .
Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



(1) Diameter on finished panel or support

- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) \emptyset 22.5 mm recommended (\emptyset 22.3 $_0^{+0.4}$) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0^{+0.016}$)