Product data sheet

Specifications





APC IT Power Distribution Module 2 Pole 3 Wire 30A L1-L2 L6-30 1400CM

PDM2330L6-12-1400

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead Time	Usually Ships within 3 Weeks

Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Provided Equipment	Installation guide

Physical

Color	Black
Height	10.00 in (25.4 cm)
Width	17.01 in (43.2 cm)
Depth	15.98 in (40.6 cm)
Net Weight	14.99 lb(US) (6.8 kg)

Input

Input Frequency	60 Hz
Max Line Current	30 A

Output

Maximum Total Current Draw Per Phase	30 A
Number Of Power Socket Outlets	1 NEMA L6-30R

Conformance

•		
Product Certifications	UL Listed	

Environmental

Ambient Air Temperature For Operation	3286 °F (030 °C)
Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	5104 °F (-1540 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Storage Relative Humidity	095 %
Storage Altitude	015000 ft (0.004572.00 m)

Ordering and shipping details

Gtin 731304285977

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	15.98 in (40.6 cm)
Package 1 Length	17.01 in (43.2 cm)
Package 1 Weight	16.98 lb(US) (7.7 kg)

Contractual warranty

Warranty 1 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information