Product data sheet

Specifications



① To be discontinued

Circuit breaker, PowerPacT P, 800A, 2 pole, 600VAC, 18kA, I-Line, ET1.0I, 80%, AC

PGA260802

(!) To be discontinued on: Apr 30, 2024

Main

Range	PowerPact	
Product Name	PowerPact P	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

Complementary

Complementary	
Line Rated Current	800 A
Number Of Poles	2P
Control Type	Toggle
Breaking Capacity Code	G
Breaking Capacity	AIR 65 kA 240 V AC 50/60 Hz UL 489 AIR 35 kA 480 V AC 50/60 Hz UL 489 AIR 18 kA 600 V AC 50/60 Hz UL 489 Icu 50 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 35 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 240 V AC 50/60 Hz IEC 60947-2 20 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, basic, ET 1.0I, I
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	ET 1.0I
Awg Gauge	3 x AWG 3/0500 kcmil aluminium/copper
Local Signalling	1 trip indicator green)
Mounting Mode	I-Line bracket)
Mounting Support	Bracket
Electrical Connection	I-Line connection, line Lugs, load
Terminal Identifier	AL800M23K
Long Time Pick-Up Adjustment Range	1 ln
Mounting Height	9 in (228.60 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (3 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.98 in (25 mm)	
Height	12.86 in (326.64 mm)	
Width	8.27 in (210.06 mm)	
Depth	8.05 in (204.47 mm)	
Net Weight	32 lb(US) (14.51 kg)	
Quantity Per Set	1	
Phase Connection	AC	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE	
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2	
Product Certifications	UL CSA NOM	
Ip Degree Of Protection	Front cover IP40	
Pollution Degree	3 IEC 60947-1	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)	
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating	

Ordering and shipping details

Category	01210-PG,H,J,K,L,N I-LINE BREAKERS	
Discount Schedule	DE2	
Gtin	785901299288	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.87 in (32.7 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	8.03 in (20.4 cm)
Package 1 Weight	35.00 lb(US) (15.876 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov