# Product data sheet

Specifications





() Discontinued

## module XPSAK - Emergency stop - 120 V AC

XPSAK351144P

() Discontinued on: Jan 23, 2021

Product availability: Stock - Normally stocked in distribution facility

### Main

Preventa Safety automation
Preventa safety module
XPSAK
For emergency stop, switch, sensing mat/edges or safety light curtain monitoring
Monitoring of electro-sensitive protection equipment (ESPE)
Multiple emergency stop monitoring 2-channel wiring
Monitoring of a movable guard
Monitoring of a movable guard associated with 2 switches and automatic start
Emergency stop monitoring 1-channel wiring
Emergency stop with 2 NC contacts monitoring 2-channel wiring
Sensing mat and edges monitoring
Proximity sensor monitoring
Can reach PL e/category 4 EN/ISO 13849-1
Can reach SILCL 3 EN/IEC 62061
DC > 99 % EN/ISO 13849-1
MTTFd = 154.5 years EN/ISO 13849-1
PFHd = 7.39E-9 1/h EN/IEC 62061
Configurable
Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm <sup>2</sup>
flexible with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm <sup>2</sup> solid with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 1 x 0.251 x 2.5 mm <sup>2</sup>
flexible with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1 mm <sup>2</sup> solid with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1.5 mm <sup>2</sup>
flexible with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 2 x 0.252 x 1 mm <sup>2</sup>
flexible with cable end, with double bezel
Captive screw clamp terminals, removable terminal block, 2 x 0.52 x 1.5 mm <sup>2</sup>
flexible with cable end, with double bezel
Relay instantaneous opening, 3 NO, volt-free
1 NC + 4 solid state outputs
120 V AC - 1510 %
24 V DC - 1510 %

### Complementary

Synchronisation Time Between Inputs	2 or 4 s depending of wiring (automatic start) Unlimited (manual start)
Supply Frequency	50/60 Hz
Maximum Power Consumption In Va	6 VA AC

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Input Protection Type	Internal, electronic
[Uc] Control Circuit Voltage	24 V DC
Maximum Line Resistance	28 Ohm
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output
Breaking Capacity	1.5 A 24 V DC-13)50 ms relay output
Output Thermal Current	6 A per relay relay output
[Ith] Conventional Free Air Thermal Current	18 A
Associated Fuse Rating	4 A gG or gL relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow relay output EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum Output Current	10 mA relay output
Minimum Output Voltage	17 V relay output
Maximum Response Time On Input Open	40 ms
[Ui] Rated Insulation Voltage	300 V 2)IEC 60947-5-1 300 V 2)DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV III IEC 60947-5-1 4 kV III DIN VDE 0110 part 1
Local Signalling	4 LEDs
Current Consumption	30 mA 24 V AC on power supply
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.88 lb(US) (0.4 kg)

## Environment

Standards	EN/IEC 60204-1 EN/ISO 13850 EN/IEC 60947-5-1 EN 1088/ISO 14119
Product Certifications	TÜV CSA UL
Ip Degree Of Protection	IP20 terminals)EN/IEC 60529 IP40 enclosure)EN/IEC 60529
Ambient Air Temperature For Operation	14131 °F (-1055 °C)
Ambient Air Temperature For Storage	-13185 °F (-2585 °C)

## Ordering and shipping details

Category	US1SAF222477
Discount Schedule	SAF2
Gtin	3389110291704
Returnability	No
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.56 in (6.5 cm)

Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	4.92 in (12.5 cm)
Package 1 Weight	16.86 oz (478.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	13.66 lb(US) (6.194 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth

#### **Dimensions Drawings**

#### Dimensions

