

Product data sheet

Specifications



Complete pre wired monolithic tower light, Harmony XVC, plastic, red orange, 60mm, base mounting, steady or flashing, with buzzer 70...85 dB,24V AC DC

XVC6B25SK

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 252.00 USD

Main

| | |
|------------------------------------|---|
| Range Of Product | Harmony XVC6 |
| Product Or Component Type | Complete pre-wired monolithic tower light |
| Beacon Or Indicator Bank Unit Type | 2 illuminated units |
| Sound Signalling | Buzzer |
| Mounting Diameter | 2.36 in (60 mm) |
| Component Name | XVC |
| Light Source | LED steady or flashing red LED steady or flashing orange |
| [Us] Rated Supply Voltage | 24 V |
| Supply Circuit Type | AC/DC |
| Noise Level | 70...85 dB continuous or intermittent tone)1 m |

Complementary

| | |
|--|--|
| Material | Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover |
| Product Mounting | On base |
| Cable Cross Section | 0.00 in² (0.33 mm²) |
| Awg Gauge | AWG 22 |
| Cable Length | 33.46 in (850 mm) |
| Marking | CE |
| [Uimp] Rated Impulse Withstand Voltage | 0.8 kV |
| Current Consumption | 90 mA |
| Fundamental Frequency | 2.23 kHz |
| Flashing Frequency | 1 Hz |
| Net Weight | 0.55 lb(US) (0.25 kg) |
| Height | 6.33 in (160.8 mm) |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Standards | IEC 61000-6-4 IEC 61000-6-3 IEC 61000-6-2 |
| Product Certifications | UL |
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -31...158 °F (-35...70 °C) |
| Ambient Air Temperature For Operation | 14...122 °F (-10...50 °C) |
| Electrical Shock Protection Class | Class II IEC 61140 |
| Ip Degree Of Protection | IP54 flat surface installation IEC 60529 |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US100XV22617 |
| Discount Schedule | 00XV |
| Gtin | 3606480032707 |
| Returnability | No |
| Country Of Origin | ID |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.39 in (8.6 cm) |
| Package 1 Width | 3.46 in (8.8 cm) |
| Package 1 Length | 19.76 in (50.2 cm) |
| Package 1 Weight | 16.93 oz (480.0 g) |
| Unit Type Of Package 2 | S04 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 11.81 in (30.0 cm) |
| Package 2 Width | 15.75 in (40.0 cm) |
| Package 2 Length | 23.62 in (60.0 cm) |
| Package 2 Weight | 15.67 lb(US) (7.109 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance


| | | |
|---------------------------|---|-----|
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |
| | | |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| China Rohs Regulation | China RoHS declaration | |
| Environmental Disclosure | Product Environmental Profile | |
| Circularity Profile | End of Life Information | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



| No. of illuminated units | b (mm) | b (in.) |
|--------------------------|--------|---------|
| 1 stage | 120.8 | 4.76 |
| 2 stages | 160.8 | 6.33 |
| 3 stages | 200.8 | 7.90 |
| 4 stages | 240.8 | 9.48 |
| 5 stages | 280.8 | 11.06 |

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Mounting on Horizontal Support (Direct or with Fixing Plate)

Panel cut-out

