Specifications





Head for triple headed push button, Harmony XB4, white flush/ red projecting/white flush pushbutton Ø22 mm with marking

ZB4BA711147

() Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony XB4 |
|-------------------------------|--|
| Product Or Component Type | Head for triple-headed push-button |
| Device Short Name | ZB4 |
| Bezel Material | Black metal |
| Mounting Diameter | 0.87 in (22 mm) |
| Sale Per Indivisible Quantity | 1 |
| Head Type | Standard |
| Shape Of Signaling Unit Head | Rectangular |
| Type Of Operator | spring return |
| Operator Profile | 2 flush - 1 central projecting STOP push-buttons |
| Operators Description | White "up arrow" - white "down arrow" - red "STOP" |

Complementary

| Net Weight | 0.12 lb(US) (0.056 kg) |
|---------------------------------------|--|
| Resistance To High Pressure Washer | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m |
| Colour Of Marking | Black marking when white caps White marking when green, red or black caps |
| Operator Profile | Red projecting, STOP white) White flush, down arrow black) White flush, up arrow black) |
| Mechanical Durability | 1000000 cycles |
| Electrical Composition Code | C1 9 single front mounting C2 9 single and double front mounting C11 3 single front mounting |
| Device Presentation | Basic element |

Environment

| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
|--|----------------------|
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Electrical Shock Protection Class | |

Electrical Shock Protection Class Class | IEC 60536

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Ip Degree Of Protection | IP69 IEC 60529 IP69K IEC 60529 | |
|---------------------------|---|--|
| Nema Degree Of Protection | NEMA 13 NEMA 4X | |
| Ik Degree Of Protection | IK06 conforming to IEC 50102 | |
| Standards | EN/IEC 60947-5-4 EN/IEC 60947-1 JIS C8201-5-1 EN/IEC 60947-5-5 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 JIS C8201-1 | |
| Product Certifications | LROS (Lloyds register of shipping) GL UL Listed BV CSA DNV | |
| Vibration Resistance | 5 gn 2500 Hz)IEC 60068-2-6 | |
| Shock Resistance | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27 | |

Ordering and shipping details

| Category | US10CS222468 |
|-------------------|---------------|
| Discount Schedule | 0CS2 |
| Gtin | 3389119044103 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.77 in (4.5 cm) |
| Package 1 Width | 1.30 in (3.3 cm) |
| Package 1 Length | 2.09 in (5.3 cm) |
| Package 1 Weight | 1.98 oz (56.0 g) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |


Dimensions Drawings

Dimensions

Without Boot




With Boot ZBA709



Product data sheet ZB4BA711147


Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)



Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer's Side)




A: 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. B: 40 mm min. Dimensions in in.



A: 1.18 in. min. **B:** 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB4 BZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
 - $_{\circ}$ every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
 - o with each selector switch head (ZB4 BD•, ZB4 BJ•, ZB4 BG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



(1) Panel

(2) Printed circuit board

Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ 01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ 01•

Dimensions An + 18.1 relate to the Ø 2.4 mm \pm 0.05 / 0.09 in. \pm 0.002 holes for centring adapter ZBZ 01.

Technical Description

Electrical Composition Corresponding to Code C1



Electrical Composition Corresponding to Code C2



Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Legend

Single contact



Double contact



Light block



Possible location

