Product data sheet

Specifications



Circuit breaker, PowerPacT P, 600A, 3 pole, 600VAC, 25kA, I-Line, Micrologic 5.0H, 100%, ABC, modbus

PJA36060CU73AE1

(!) To be discontinued on: Apr 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 34,593.00 USD

Main

Range	PowerPact
Product Name	PowerPact P
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

compromontary	
Line Rated Current	600 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	J
Breaking Capacity	AIR 100 kA 240 V AC 50/60 Hz UL 489 AIR 65 kA 480 V AC 50/60 Hz UL 489 AIR 25 kA 600 V AC 50/60 Hz UL 489 Icu 65 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 50 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	35 kA 240 V AC 50/60 Hz IEC 60947-2 25 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, harmonic, MicroLogic 5.0 H, LSI
Continuous Current Rating	100 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 5.0 H
Accessory / Separate Part Type	Modbus connecting cable
Awg Gauge	3 x AWG 3/0500 kcmil aluminium/copper
Local Signalling	1 trip indicator green)
Mounting Mode	I-Line bracket)
Mounting Support	Bracket

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Connection	I-Line connection, line	
	Lugs, load	
Terminal Identifier	AL800M23K	
Long Time Pick-Up Adjustment Range	0.41 x lr	
Mounting Height	9 in (228.60 mm)	
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (3 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	0.98 in (25 mm)	
Height	12.86 in (326.64 mm)	
Width	8.27 in (210.06 mm)	
Depth	8.05 in (204.47 mm)	
Net Weight	32 lb(US) (14.51 kg)	
Quantity Per Set	1	
Phase Connection	ABC	
Communication Interface	Modbus	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	UL
	CSA
	NEMA
	NOM-003-SCFI-2000
	IEC 60947-2
Product Certifications	UL
	CSA
	NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating
	13123.36 ft (4000 m) with derating

Ordering and shipping details

<u></u>		
Category	US10DE201210	
Discount Schedule	0DE2	
Returnability	Yes	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	32.00 lb(US) (14.515 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov