





Circuit breaker, PowerPacT P, 1000A, 3 pole, 600VAC, 25kA, lugs, Micrologic 3.0, 100%, kirk lock

PJP36100CU31AJK

! To be discontinued on: Apr 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	PowerPact	
Product Name	PowerPact P	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

### Complementary

Line Rated Current	1000 A
Number Of Poles	3P
Control Type	Toggle
Breaking Capacity Code	J
Breaking Capacity	AIR 100 kA 240 V AC 50/60 Hz UL 489 AIR 65 kA 480 V AC 50/60 Hz UL 489 AIR 25 kA 600 V AC 50/60 Hz UL 489 Icu 65 kA 240 V AC 50/60 Hz IEC 60947-2 Icu 50 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Ue] Rated Operational Voltage	600 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	35 kA 240 V AC 50/60 Hz IEC 60947-2 25 kA 380/415 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Electronic, standard, MicroLogic 3.0, LI
Continuous Current Rating	100 %
[Ui] Rated Insulation Voltage	750 V IEC 60947-2
Trip Unit Name	MicroLogic 3.0
Accessory / Separate Part Type	Keylock accessories
Awg Gauge	4 x AWG 3/0500 kcmil aluminium/copper
Local Signalling	Overload 1 1 LED amber) 1 trip indicator green)
Mounting Mode	Unit mount lug)
Mounting Support	Lug
Electrical Connection	Terminal nut, line Lugs, load

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Terminal Identifier	AL1200P25K	
Long Time Pick-Up Adjustment Range	0.41 x lr	
Tightening Torque	442.54 lbf.in (50 N.m) 0.150.37 in² (95240 mm²) (4 x AWG 3/0500 kcmil) 8.8511.51 lbf.in (1.01.3 N.m)	
Number Of Slots	2 auxiliary switch OF plug-in) 1 alarm switch SD plug-in) 1 overcurrent trip switch SDE plug-in) 1 voltage release MN or MX plug-in)	
Power Wire Stripping Length	1.18 in (30 mm)	
Type Of Keylock	Kirk	
Height	16.16 in (410.46 mm)	
Width	8.27 in (210.06 mm)	
Depth	8.05 in (204.47 mm)	
Net Weight	32 lb(US) (14.51 kg)	
Quantity Per Set	1	
Circuit Breaker Application	HACR rated	

### **Environment**

Quality Labels	CE
Standards	UL CSA NEMA NOM-003-SCFI-2000 IEC 60947-2
Product Certifications	UL CSA NOM
Ip Degree Of Protection	Front cover IP40
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	< 6561.68 ft (2000 m) without derating 13123.36 ft (4000 m) with derating

# Ordering and shipping details

Category	01215 - PG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Returnability	No
Country Of Origin	US

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.14 in (41.0 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	8.03 in (20.4 cm)

Package 1 Weight

32.00 lb(US) (14.515 kg)

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov