

Product data sheet

Specifications



Mini circuit breaker, QO, 15A, 1 pole, 120VAC, 22kA, plug in, dual function, plug on neutral

QO115VHPDF

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	15 A
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Circuit Breaker Type	Combination ARC-fault and ground fault
Ratings	HACR rated
Electrical Connection	Pressure plate
Connections Terminals	Plug-on neutral

Complementary

Interrupt Rating	22 kA 120 V AC
Number Of Panel Spaces	1
Wire Size	AWG 14...AWG 8 copper
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	4.76 in (121 mm)
Width	0.75 in (19 mm)
Depth	2.91 in (74 mm)
Net Weight	0.25 lb(US) (0.113 kg)

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	US1DE2A06303
Discount Schedule	DE2A
Gtin	00785901860532
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	MX
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.74 in (12.04 cm)
Package 1 Width	0.74 in (1.88 cm)
Package 1 Length	2.84 in (7.214 cm)
Package 1 Weight	4.00 oz (113.398 g)

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive		Compliant
		EU RoHS Declaration
China Rohs Regulation		China RoHS declaration