





Mini circuit breaker, QO, 15A, 2 pole, 120/240VAC, 22kA, plug in, AC shunt

QO215VH1021

! Discontinued on: Sep 19, 2022

① Discontinued

Main

Product	Miniature circuit-breaker	
Range	QO	
Current Rating	15 A	
Voltage Rating	120/240 V AC 120 V AC	
Mounting Type	Plug-in	
Number Of Poles	2P	
Circuit Breaker Type	Standard	
Ratings	HACR rated	
Electrical Connection	Pressure plate	
Options	Shunt trip 120/208/240 V AC	

Complementary

Interrupt Rating	22 kA 120/240 V AC 22 kA 120 V AC	
Number Of Panel Spaces	3	
Wire Size	AWG 14AWG 8 copper or aluminium	
Tightening Torque	49.56 lbf.in (5.6 N.m)	
Height	2.99 in (76 mm)	
Width	2.24 in (57 mm)	
Depth	2.91 in (74 mm)	
Net Weight	0.93 lb(US) (0.422 kg)	

Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00926-QO IND SPECIALTY CB
Discount Schedule	DE2A
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.20 in (8.128 cm)
Package 1 Width	3.60 in (9.144 cm)
Package 1 Length	4.70 in (11.938 cm)
Package 1 Weight	14.88 oz (421.841 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration