Specifications





Head for key switch selector, Harmony XB5, plastic, black, 22mm, key 455, 2 positions, stay put

ZB5AG02

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 90.00 USD

Main

| Range Of Product | Harmony XB5 | | | |
|-------------------------------|------------------------------|--|--|--|
| | | | | |
| Product Or Component Type | Head for key selector switch | | | |
| Device Short Name | ZB5 | | | |
| Bezel Material | Dark grey plastic | | | |
| Mounting Diameter | 0.87 in (22 mm) | | | |
| Head Type | Standard | | | |
| Sale Per Indivisible Quantity | 1 | | | |
| Shape Of Signaling Unit Head | Round | | | |
| Type Of Operator | stay put | | | |
| Operator Profile | Black key switch | | | |
| Operator Position Information | 2 positions 90° | | | |
| Type Of Keylock | Key 455 | | | |
| Key Withdrawal Position | Right | | | |

Complementary

| Cad Overall Width | 1.14 in (29 mm) | | | | |
|-----------------------------|---|--|--|--|--|
| Cad Overall Height | 1.14 in (29 mm) | | | | |
| Cad Overall Depth | 2.83 in (72 mm) | | | | |
| Mechanical Durability | 1000000 cycles | | | | |
| Station Name | XALD 15 cut-outs XALK 25 cut-outs | | | | |
| Electrical Composition Code | C4 6 single and double front mounting C5 5 single front mounting C6 5 single and double front mounting C7 4 single front mounting C8 4 single and double front mounting C11 3 single front mounting C3 6 single front mounting SF1 3 single front mounting SR1 3 single rear mounting C15 1 single front mounting | | | | |
| Device Presentation | Basic element | | | | |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Protective Treatment | тн | | | | | |
|---------------------------------------|---|--------------------|--|--|--|--|
| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) | | | | | |
| Ambient Air Temperature For Operation | -40158 °F (-4070 °C) | | | | | |
| Overvoltage Category | Class II IEC 60536 | Class II IEC 60536 | | | | |
| Ip Degree Of Protection | IP66 IEC 60529 IP67 IP69 IP69K | | | | | |
| Nema Degree Of Protection | NEMA 13 NEMA 4X | | | | | |
| Resistance To High Pressure Washer | 1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m | | | | | |
| Ik Degree Of Protection | IK06 conforming to IEC 50102 | | | | | |
| Standards | UL 508 IEC 60947-5-4 JIS C8201-5-1 IEC 60947-1 IEC 60947-5-1 CSA C22.2 No 14 JIS C8201-1 | | | | | |
| Product Certifications | UL Listed CSA BV GL LROS (Lloyds register of shipping) DNV | | | | | |
| Vibration Resistance | 5 gn 2500 Hz)IEC 60068-2-6 | | | | | |
| Shock Resistance | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27 | | | | | |

Ordering and shipping details

| Category | US10CS222467 | | | |
|-------------------|---------------|--|--|--|
| Discount Schedule | 0CS2 | | | |
| Gtin | 3389110651867 | | | |
| Returnability | No | | | |
| Country Of Origin | FR | | | |

Packing Units

| Unit Type Of Package 1 | PCE | | |
|------------------------------|------------------------|--|--|
| Number Of Units In Package 1 | 1 | | |
| Package 1 Height | 2.13 in (5.4 cm) | | |
| Package 1 Width | 3.46 in (8.8 cm) | | |
| Package 1 Length | 1.34 in (3.4 cm) | | |
| Package 1 Weight | 1.76 oz (50.0 g) | | |
| Unit Type Of Package 2 | S02 | | |
| Number Of Units In Package 2 | 50 | | |
| Package 2 Height | 5.91 in (15.0 cm) | | |
| Package 2 Width | 11.81 in (30.0 cm) | | |
| Package 2 Length | 15.75 in (40.0 cm) | | |
| Package 2 Weight | 8.50 lb(US) (3.855 kg) | | |

Contractual warranty

Warranty

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

| Reach Regulation | REACh Declaration | | | |
|---------------------------|---|--|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | | |
| China Rohs Regulation | China RoHS declaration | | | |
| Environmental Disclosure | Product Environmental Profile | | | |
| Circularity Profile | End of Life Information | | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | | |

ZB5AG02

Dimensions Drawings


Dimensions



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 in. $_0^{+0.016}$)

| | | | | • |
|---|---------|----------|---------|----------|
| Connections | a in mm | a in in. | b in mm | b in in. |
| By screw clamp terminals or plug-in connector | 40 | 1.57 | 30 | 1.18 |
| By Faston connectors | 45 | 1.77 | 32 | 1.26 |
| On printed circuit board | 30 | 1.18 | 30 | 1.18 |


Detail of Lug Recess



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended. (3) \emptyset 22.5 mm recommended (\emptyset 22.3 $_0^{+0.4}$) / \emptyset 0.89 in. recommended (\emptyset 0.88 in. $_0^{+0.016}$)

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection


Panel Cut-outs (Viewed from Installer's Side)




A: 30 mm min. / 1.18 in. min. **B:** 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min. **B:** 40 mm min.



A: 1.18 in. min. **B:** 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

Installation Precautions

- $_{\bullet}$ Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2 30' (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
 - $_{\circ}~$ every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
 - o with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut

10

(4) Printed circuit board

Mounting of Adapter (Socket) ZBZ01•


- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ01•


Dimensions An + 18.1 relate to the Ø 2.4 mm \pm 0.05 / 0.09 in. \pm 0.002 holes for centring adapter ZBZ01•.

ZB5AG02


Technical Description









13







ZB5AG02

Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1



Legend

Single contact



Double contact



Light block



Possible location



Sequence of Contacts Fitted to 2-position Selector Switch Body

Position 315°



| Push | Position | Тор | | | | |
|----------|----------|--------|--------|--------|------------------|--|
| | | Bottom | | | \triangleright | |
| | Location | | Left | Centre | Right | |
| | State | | 0 | 0 | 0 | |
| Contacts | N/O | | open | open | open | |
| | N/C | | closed | closed | closed | |

Position 45°



| Push | | Тор | | | |
|----------|----------|--------|--------|--------|--------|
| | Position | Bottom | | | |
| | Location | | Left | Centre | Right |
| | State | | 1 | 1 | 1 |
| Contacts | N/O | | closed | closed | closed |
| | N/C | | open | open | open |