Product data sheet

Specification





Complete body for push buttons or selector switches, Harmony XB6, single contact, with body fixing collar, faston connector, 1NC

ZB6Z2B

Product availability: Stock - Normally stocked in distribution facility

Price*: 9.40 USD

Main

Range Of Product	Harmony XB6
Product Or Component Type	Complete body for push-buttons or selector switches
Device Short Name	ZB6
Fixing Collar Material	Plastic
Sale Per Indivisible Quantity	1
Contacts Type And Composition	1 NC
Contact Operation	Slow-break
Connections - Terminals	Faston connector Faston connector 2.8 x 0.5 mm
[Us] Rated Supply Voltage	<= 250 V

Complementary

Cad Overall Width	0.71 in (18 mm)
Cad Overall Height	0.71 in (18 mm)
Cad Overall Depth	1.57 in (40 mm)
Terminals Description Iso N°1	(11-12)NC
Net Weight	0.01 lb(US) (0.004 kg)
Contacts Usage	Standard
Positive Opening	With IEC 60947-5-1 appendix K
Operating Travel	0.04 in (1 mm) NC changing electrical state) 0.17 in (4.3 mm) total travel)
Operating Force	2.5 N NC changing electrical state
Contacts Material	Silver alloy (Ag/Ni)
Short-Circuit Protection	6 A cartridge fuse gG IEC 60947-5-1
[le] Rated Operational Current	3 A 120 V, AC-15, B300 1.5 A 240 V, AC-15, B300 0.1 A 250 V, DC-13, R300 0.22 A 125 V, DC-13, R300
Electrical Durability	1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-15, 2 A 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C
Electrical Reliability	Λ = 10exp(-8) 5 V 1 mA with confidence level of 90 % IEC 60947-5-4

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP65 IEC 60529
Standards	IEC 60947-5-1 JIS C 852 JIS C 4520 UL 508 CSA C22.2 No 14 IEC 60947-5-5 IEC 60947-1
Product Certifications	GOST UL CCC CSA
Vibration Resistance	+/- 3 mm 2500 Hz)IEC 60068-2-6 5 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	US10CS222459
Discount Schedule	0CS2
Gtin	3389110775341
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	2.76 in (7.0 cm)
Package 1 Weight	0.21 oz (6.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	100
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	28.68 oz (813.0 g)

Contractual warranty



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

ZB6Z2B

Dimensions Drawings

Body for Pushbutton, Selector Switch or Key Switch

Dimensions

