Product data sheet

Specifications





frequency control relay, Harmony Control Relays, 5A, 1CO+1CO, 120…277V AC

RM35HZ21FM

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 222.00 USD

Main

Harmony Control Relays	
Frequency control relays	
Frequency control relay	
RM35HZ21FM	
Overfrequency and underfrequency 50 or 60 Hz	
Adjustable 0.110 s, +/- 10 % Tt- time delay upon fault	
1250 VA	
10 mA 5 V DC	
6 VA AC	
4070 Hz	
AC-12 IEC 60947-5-1 AC-13 IEC 60947-5-1 AC-14 IEC 60947-5-1 AC-15 IEC 60947-5-1 DC-12 IEC 60947-5-1 DC-13 IEC 60947-5-1 DC-14 IEC 60947-5-1	

Complementary

Reset Time	2000 ms time delay	
Maximum Switching Voltage	250 V AC/DC	
[Us] Rated Supply Voltage	120277 V AC	
[Un] Rated Nominal Voltage	120277 V AC, non self-powered	
Supply Voltage Limits	102308 V AC	
Control Circuit Frequency	4070 Hz	
Width	1.38 in (35 mm)	
Output Contacts	1 C/O + 1 C/O	
Contacts Material	Cadmium free	
Nominal Output Current	5 A	
Maximum Input Frequency	70 Hz	
Maximum Measuring Cycle	200 ms measurement cycle as true rms value	
Delay At Power Up	0.5 s	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Hysteresis	0.3 % fixed	
Measurement Accuracy	+/- 10 % of the full scale value in input +/- 10 % of the full scale value in time delay	
Repeat Accuracy	+/- 0.5 % input and measurement circuit +/- 0.5 % time delay	
Measurement Error	+/- 0.05 %/°C with temperature variation < +/- 1 % over the whole range with voltage variation	
Threshold Setting	-210 Hz -102 Hz	
Marking	CE : 73/23/EEC CE : EMC 89/336/EEC	
Overvoltage Category	III IEC 60664-1	
Insulation Resistance	 > 500 MOhm 500 V DC between supply and relay output IEC 60255-5 > 500 MOhm 500 V DC between measurement and relay output IEC 60664-1 > 1 MOhm 500 V DC between supply and measurement IEC 60255-5 > 500 MOhm 500 V DC between supply and relay output IEC 60664-1 > 500 MOhm 500 V DC between measurement and relay output IEC 60255-5 > 1 MOhm 500 V DC between supply and measurement IEC 60664-1 	
[Ui] Rated Insulation Voltage	400 V IEC 60664-1	
Operating Voltage Tolerance	- 15 % + 10 % Un	
Supply Frequency	50/60 Hz +/- 10 %	
Insulation	No galvanic insulation between supply and measurement	
Operating Position	Any position without derating	
Connections - Terminals	Screw terminals, 1 x 0.51 x 4 mm ² AWG 20AWG 11) solid without cable end Screw terminals, 2 x 0.52 x 2.5 mm ² AWG 20AWG 14) solid without cable end Screw terminals, 1 x 0.21 x 2.5 mm ² AWG 24AWG 12) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm ² AWG 24AWG 16) flexible with cable end	
Tightening Torque	5.318.85 lbf.in (0.61 N.m) IEC 60947-1	
Housing Material	Self-extinguishing plastic	
Local Signalling	1 LED Green power ON 1 LED Yellow correct frequency (high R1) 1 LED Yellow correct frequency (low R2)	
Mounting Support	35 mm symmetrical DIN rail conforming to IEC 60715	
Electrical Durability	100000 cycles	
Mechanical Durability	3000000 cycles	
Operating Rate	<= 360 operations/hour full load	
Control Type	Without test button	

Environment

Immunity To Microbreaks	10 ms
Electromagnetic Compatibility	Emission standard for industrial environments IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments IEC 61000-6-3 Immunity for industrial environments NF EN/IEC 61000-6-2
Standards	IEC 60255-6 NF EN 60255-6
Product Certifications	GL UL CSA C-tick GOST
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)

Ambient Air Temperature For Operation	-4122 °F (-2050 °C)
Relative Humidity	95 % 131 °F (55 °C) IEC 60068-2-30
Vibration Resistance	0.35 mm 557.6 Hz)IEC 60068-2-6/IEC 60255-21-1 1 gn 57.6150 Hz)IEC 60068-2-6/IEC 60255-21-1
Shock Resistance	15 gn 11 ms IEC 60255-21-1
Ip Degree Of Protection	IP20 IEC 60529 terminals) IP30 IEC 60529 casing)
Pollution Degree	3 IEC 60664-1
Dielectric Test Voltage	2 kV AC 50 Hz
Non-Dissipating Shock Wave	4 KV

Ordering and shipping details

Category	US10CP222380	
Discount Schedule	0CP2	
Gtin	3389119405201	
Returnability	No	
Country Of Origin	ID	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.81 in (4.600 cm)
Package 1 Width	3.15 in (8.000 cm)
Package 1 Length	3.82 in (9.700 cm)
Package 1 Weight	4.44 oz (126.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	48
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	15.08 lb(US) (6.838 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Product data sheet

Dimensions Drawings

Frequency Control Relay

Dimensions and Mounting






Connections and Schema

Frequency Control Relay


Wiring Diagram




Technical Description

Function Diagrams

Over-Frequency and Under-Frequency Control on 50 Hz or 60 Hz Supplies Without memory ("No Memory" mode)



With memory ("Memory" mode)



Legend

Tt Time delay after crossing of threshold from 0.1 s to 10 s Un Supply voltage F Monitored frequency H Hysteresis F> Over-frequency threshold F< Under-frequency threshold 11-12, 11-14 R1 output relay connections 21-22, 21-24 R2 output relay connections Relay status: black color = energized.

NOTE: In "Memory" mode, the relay opens after the time delay and stays in that position when crossing of the threshold is detected. The power supply voltage must be switched off to reset the product.