Product data sheet

Specifications





Harmony, Power plug-in relay, 15 A, 2 CO, with LED, 230 V AC

RPM23P7

! Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

① Discontinued

Main

Range Of Product	Harmony Electromechanical Relays	
Series Name	Power	
Product Or Component Type	Plug-in relay	
Device Short Name	RPM	
Contacts Type And Composition	2 C/O	
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz	
[Ithe] Conventional Enclosed Thermal Current	15 A -40131 °F (-4055 °C)	
Status Led	With	
Control Type	Without lockable test button	
Utilisation Coefficient	20 %	

Complementary

Complementary	
Shape Of Pin	Flat
[Ui] Rated Insulation Voltage	250 V IEC 300 V CSA
	300 V UL
[Uimp] Rated Impulse Withstand Voltage	4 kV 1.2/50 μs
Contacts Material	AgNi
[le] Rated Operational Current	15 A 277 V AC) UL
	15 A 28 V DC) UL
	15 A 250 V AC) NO IEC
	15 A 28 V DC) NO IEC
	7.5 A 250 V AC) NC IEC
	7.5 A 28 V DC) NC IEC
	7.5 A 20 V DC) NO IEC
Maximum Switching Voltage	250 V IEC
Resistive Load Current	15 A 250 V AC
	15 A 28 V DC
Maximum Switching Capacity	3750 VA
	420 W
Minimum Switching Capacity	170 mW 10 mA, 17 V
Operating Rate	<= 1200 cycles/hour under load
	<= 18000 cycles/hour no-load
Mechanical Durability	10000000 cycles
Electrical Durability	100000 cycles resistive
Average Coil Consumption In Va	1.1 60 Hz

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Drop-Out Voltage Threshold	>= 0.15 Uc AC
Operate Time	20 ms at nominal voltage
Release Time	20 ms at nominal voltage
Average Coil Resistance	16270 Ohm at 68 °F (20 °C) +/- 15 %
Rated Operational Voltage Limits	184253 V AC
Protection Category	RTI
Test Levels	Level A group mounting
Operating Position	Any position
Pollution Degree	3
Safety Reliability Data	B10d = 100000
Net Weight	0.08 lb(US) (0.036 kg)
Device Presentation	Complete product

Environment

Dielectric Strength	1500 V AC between contacts with micro disconnection 2000 V AC between coil and contact with reinforced 2000 V AC between poles with basic	
Standards	CSA C22.2 No 14 UL 508 EN/IEC 61810-1	
Product Certifications	UL CSA EAC	
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)	
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)	
Vibration Resistance	3 gn +/- 1 mm 10150 Hz)5 cycles in operation 5 gn +/- 1 mm 10150 Hz)5 cycles not operating	
Degree Of Protection (Housing Only)	IP40 conforming to EN/IEC 60529	
Shock Resistance	15 gnin operation 30 gnnot operating	

Ordering and shipping details

Category	US10CP221127
Discount Schedule	0CP2
Gtin	3389119218047
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.06 in (2.7 cm)
Package 1 Width	0.83 in (2.1 cm)
Package 1 Length	1.54 in (3.9 cm)
Package 1 Weight	1.27 oz (36.0 g)

Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.22 in (3.1 cm)
Package 2 Width	4.02 in (10.2 cm)
Package 2 Length	4.92 in (12.5 cm)
Package 2 Weight	13.97 oz (396.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	120
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	11.19 lb(US) (5.075 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information


Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions




Pin Side View



RPM23P7

Connections and Schema

Wiring Diagram




Symbols shown in blue correspond to Nema marking.

RPM23P7

Performance Curves

Electrical Durability of Contacts


Durability (inductive load) = durability (resistive load) x reduction coefficient. Resistive AC load



X Switching capacity (kVA)


Y Durability (Number of operating cycles)

Reduction coefficient for inductive AC load (depending on power factor cos φ)



Y Reduction coefficient (A)

Maximum switching capacity on resistive DC load



X Voltage DC

Y Current DC

Note: These are typical curves, actual durability depends on load, environment, duty cycle, etc.