

Product datasheet

Specifications



cam voltmeter switch CMV - 3L and 3L-N - 45° - for Ø 22.3 mm

16018

Main

Range Of Product	PowerLogic
Product Or Component Type	Selector switch
Device Short Name	CMV
Device Application	Voltmeter selector
[Ue] Rated Operational Voltage	500 V

Complementary

Mounting Mode	Flush-mounted
Mounting Support	Front face
Height	48 mm
Width	48 mm
Depth	69 mm
Mechanical Durability	2000000 cycles
Electrical Durability	100000 cycles

Environment

Standards	IEC 60947-3
Ambient Air Temperature For Operation	-25...50 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.300 cm
Package 1 Width	7.300 cm
Package 1 Length	7.300 cm
Package 1 Weight	122.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	80
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.277 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	