Product datasheet

Specifications





Multi9 - C60 UL1077 - MCB - 1P - 35 A - B Curve - 277 V - 5 kA

17408

Discontinued on: Jan 23, 2021

① Discontinued

Main

Range	Multi9	
Product Name	Multi9 C60	
Product Or Component Type	Miniature circuit-breaker	
Device Short Name	C60 UL1077	
Device Application Distribution		
Poles Description	1P	
Number Of Protected Poles	1	
[In] Rated Current	35 A at 25 °C	
Network Type	DC AC	
Trip Unit Technology	Thermal-magnetic	
Curve Code	В	
Breaking Capacity		
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	

Complementary

Network Frequency	50/60 Hz	
[Ue] Rated Operational Voltage	415 V AC 240 V AC 60 V DC	
Magnetic Tripping Limit	4 x ln +/- 20 % AC 5.6 x ln +/- 20 % DC	
Limitation Class	3 conforming to EN/IEC 60947-2	
[Ui] Rated Insulation Voltage	500 V AC conforming to EN/IEC 60947-2	
[Uimp] Rated Impulse Withstand Voltage	npulse Withstand 6 kV conforming to EN/IEC 60947-2	
Contact Position Indicator	Yes	

Apr 26, 2024 Life Is On Schneider

Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
9 Mm Pitches	2	
Height	81 mm	
Width	18 mm	
Depth	73 mm	
Net Weight	0.11 kg	
Colour	Grey	
Mechanical Durability	20000 cycles	
Electrical Durability	10000 cycles	
Provision For Padlocking	Padlockable	
Connections - Terminals	Tunnel type terminal (top or bottom)2.535 mm² (AWG 14AWG 2) - rigid	
Wire Stripping Length	14 mm for top or bottom connection	
Tightening Torque	3.5 N.m top or bottom	

Environment

Standards	UL 1077 GB 14048.2 EN/IEC 60947-2 CSA C22.2 No 235	
Product Certifications	UR CSA CCC IEC	
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529	
Pollution Degree	3 conforming to EN/IEC 60947-2	
Overvoltage Category	IV	
Tropicalisation	2 conforming to IEC 60068-1	
Relative Humidity	95 % at 55 °C	
Operating Altitude	2000 m	
Ambient Air Temperature For Operation	-3070 °C	
Ambient Air Temperature For Storage	-4080 °C	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2 cm
Package 1 Length	9 cm
Package 1 Weight	123.671 g

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins