



complete manual source changeover assembly, FXM400, Compact INS400 switch disconnectors, 400 A, 4 poles

31151

#### Main

Range Of Product	INS320630
Range	TransferPacT ComPact
Device Short Name	INS400
Product Or Component Type	Manual transfer switch
Device Application	Change source of supply
Range Compatibility	ComPact ComPacT INS INS400 switch disconnector
Poles Description	4P
Network Type	AC DC
Network Frequency	50/60 Hz
Mounting Mode	Fixed
Upside Connection	Front
Downside Connection	Front
Suitability For Isolation	Yes
Contact Position Indicator	Yes
[Icm] Rated Short-Circuit Making Capacity	330 kA with upstream protection circuit breaker 690 V AC at 50/60 Hz 50 kA switch-disconnector alone 690 V AC at 50/60 Hz

## Complementary

Transfer Switch Class	PC
Number Of Contact Position	3
Control Type	Direct front rotary handle
Operating Mode	Manual
Mounting Support	Rail Plate
Locking Options Description	Padlocking in OFF position

[le] Rated Operational Current	AC-22A: 400 A AC 50/60 Hz 220/240 V AC-22A: 400 A AC 50/60 Hz 380/415 V
	AC-22A: 400 A AC 50/60 Hz 440/480 V
	AC-22A: 400 A AC 50/60 Hz 500/525 V
	AC-22A: 400 A AC 50/60 Hz 660/690 V
	AC-23A: 400 A AC 50/60 Hz 220/240 V
	AC-23A: 400 A AC 50/60 Hz 380/415 V AC-23A: 400 A AC 50/60 Hz 440/480 V
	AC-23A: 400 A AC 50/60 Hz 500/525 V
	AC-23A: 400 A AC 50/60 Hz 660/690 V
	DC-22A: 400 A DC 125 V 2 poles in series
	DC-23A: 400 A DC 125 V 2 poles in series
	DC-22A: 400 A DC 250 V 4 poles in series DC-23A: 400 A DC 250 V 4 poles in series
	DO-20A. 400 A DO 200 V 4 poles ili series
[Ith] Conventional Free Air Thermal Current	400 A at 60 °C
Rated Duty	Uninterrupted
Intermittent Duty Class	Class 120 - 60 %
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-3 250 V DC conforming to IEC 60947-3
Mechanical Interlocking	With mechanical interlocking
Mechanical Durability	10000 cycles
Electrical Durability	AC-22A: 1500 cycles 440 V AC 50/60 Hz
•	AC-22A: 1500 cycles 500 V AC 50/60 Hz
	AC-22A: 1500 cycles 690 V AC 50/60 Hz
	AC-23A: 1500 cycles 440 V AC 50/60 Hz
	AC-23A: 1500 cycles 500 V AC 50/60 Hz
	AC-23A: 1500 cycles 690 V AC 50/60 Hz DC-23A: 1000 cycles 250 V DC 4 poles in series
Connection Pitch	45 mm
[Icw] Rated Short-Time Withstand	11.5 kA during 3 s conforming to IEC 60947-3
Current	20 kA during 1 s conforming to IEC 60947-3
	4 kA during 30 s conforming to IEC 60947-3
	4.9 kA during 20 s conforming to IEC 60947-3
Height	205 mm
Width	395 mm
Depth	155 mm
Net Weight	13.5 kg
Environment	
Livironinient	
Standards	IEC 60947-3 IEC 60947-1
Product Certifications	СВ
Electrical Shock Protection Class	Class II
Ip Degree Of Protection	IP40 conforming to IEC 60947-3
Pollution Degree	3
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C
Packing Units	
Unit Type Of Package 1	PCE
	. 02

Number Of Units In Package 1	1
Package 1 Height	20 cm
Package 1 Width	23 cm
Package 1 Length	50 cm
Package 1 Weight	15 kg

# **Contractual warranty**

Warranty 18 months

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins