



Main

Range	Vigirex
Device short name	RH99P
Product or component type	Monitoring relay
Relay application	Monitoring relay
Mounting support	Front panel
Type of setting	Selector
Residual earth-leakage sensitivity adjustment type	Adjustable 9 settings
Earth-leakage sensitivity	0.03...30 A
Earth-leakage time delay	Instantaneous for 0.03 A Adjustable 9 settings 0...4.5 s for 0.03...30 A
Threshold setting	0.03...30 A alarm
Current sensors compatibility	TOA earth leakage current sensor A earth leakage current sensor L earth leakage current sensor
[I _{th}] conventional enclosed thermal current	8 A
Minimum load	10 mA at 12 V
[U _s] rated supply voltage	220...240 V AC 50/60 Hz 70...110 %
Power consumption in VA	4 VA
Monitored distribution system	1000 V - AC at 50/60 Hz (maximum) 1000 V - AC at 400 Hz (maximum)
Earthing system	TN-S TT

Complementary

Test function	Local
---------------	-------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	Remote test
Monitoring	Electronics (continuous) Power supply (continuous) Relay/sensor link (continuous)
Type of measurement	Earth fault current internal measurement, range: 80...100 %
Tamperproof of settings	Protected by sealable cover
Connections - terminals	Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm ² flexible AWG 24...AWG 12 Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm ² rigid AWG 24...AWG 12 Auxiliary power supply: terminal block cable(s) 0.25...2.5 mm ² flexible with ferrule AWG 24...AWG 12 Fault: terminal block cable(s) 0.2...2.5 mm ² flexible AWG 24...AWG 12 Fault: terminal block cable(s) 0.2...2.5 mm ² rigid AWG 24...AWG 12 Fault: terminal block cable(s) 0.25...2.5 mm ² flexible with ferrule AWG 24...AWG 12 Relay test and fault reset: terminal block cable(s) 0.2...2.5 mm ² flexible AWG 24...AWG 12 Relay test and fault reset: terminal block cable(s) 0.2...2.5 mm ² rigid AWG 24...AWG 12 Relay test and fault reset: terminal block cable(s) 0.25...2.5 mm ² flexible with ferrule AWG 24...AWG 12 Sensor: terminal block cable(s) 0.2...2.5 mm ² flexible AWG 24...AWG 12 Sensor: terminal block cable(s) 0.2...2.5 mm ² rigid AWG 24...AWG 12 Sensor: terminal block cable(s) 0.25...2.5 mm ² flexible with ferrule AWG 24...AWG 12 Voltage presence: terminal block cable(s) 0.2...2.5 mm ² flexible AWG 24...AWG 12 Voltage presence: terminal block cable(s) 0.2...2.5 mm ² rigid AWG 24...AWG 12 Voltage presence: terminal block cable(s) 0.25...2.5 mm ² flexible with ferrule AWG 24...AWG 12
Wire stripping length	Auxiliary power supply: 7 mm Fault: 7 mm Relay test and fault reset: 7 mm Sensor: 7 mm Voltage presence: 7 mm
Tightening torque	Auxiliary power supply: 0.6 N.m Fault: 0.6 N.m Relay test and fault reset: 0.6 N.m Sensor: 0.6 N.m Voltage presence: 0.6 N.m
Width	72 mm
Height	72 mm
Depth	78 mm
Cut-out dimensions	68 x 68 mm
Net weight	0.3 kg
IP degree of protection	IP40 on front face: conforming to EN/IEC 60529 IP30 on side parts: conforming to EN/IEC 60529 IP20 on connection terminals: conforming to EN/IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Mechanical robustness	Fire resistance conforming to IEC 60695-2-1 IK protection 2 joules: IK07 conforming to EN 50102 Vibrations 13.2...100 Hz: 0.7 g Vibrations 2...13.2 Hz: +/- 1 mm

Environment

Overvoltage category	IV
Electrical shock protection class	Class II
Electromagnetic compatibility	Conducted and radiated emissions: , B, conforming to CISPR 11 Conducted radio-frequency immunity test: , 3, conforming to IEC 61000-4-6 Electrostatic discharge immunity test: , 4, conforming to IEC 61000-4-2 High-energy conducted susceptibility: , 4, conforming to IEC 61000-4-5 Low-energy conducted susceptibility: , 4, conforming to IEC 61000-4-4 Radiated susceptibility: , 3, conforming to IEC 61000-4-3
Relative humidity	95 % at 55 °C
Pollution degree	3 conforming to IEC 60664-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Weight	306 g
Package 1 Height	7.8 cm
Package 1 width	8.7 cm
Package 1 Length	9.3 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------