

Product datasheet

Specifications



impulse relay iTLs - 1P - 1NO - 16A - coil 110 VDC - 230...240 VAC 50/60Hz

A9C32811

! Discontinued - Service only

! Discontinued on: Jan 23, 2021

! End-of-service on: Jan 24, 2021

Main

Range Of Product	Acti9
Product Name	Acti9 iTL
Product Or Component Type	Impulse relay
Device Short Name	iTLs
Device Application	Remote indication
Poles	1P
Pole Contact Composition	1 NO
Auxiliary Contact Composition	1 C/O
[In] Rated Current	16 A
Network Type	AC
[Uc] Control Circuit Voltage	230...240 V AC 50/60 Hz 110 V DC

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	250 V AC 50/60 Hz
Control Type	Coil disconnection Remote and manual control
Control Signal Type	Impulse
Switching Frequency	100 switching operations/day 5 switching operations/minute
Impulse Duration	50 ms...1 s
Remote Control Type	Illuminated push-button 3 mA
Local Signalling	ON/OFF indication
Signalling Circuit Voltage	AC: 24...240 V DC: 24...240 V
Signalling Output Current	0.01...6 A
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	2
Height	84 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	18 mm
Depth	60 mm
Electrical Durability	AC-21: 200000 cycles AC-22: 100000 cycles
Connections - Terminals	Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm² rigid Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm² rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 1...4 mm² flexible Control circuit: tunnel type terminals 1 cable(s) 1...4 mm² flexible with ferrule Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² rigid Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² rigid with cable end Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² flexible Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² flexible with ferrule
Wire Stripping Length	11 mm
Tightening Torque	1 N.m
Range Compatibility	Acti 9 iATEt Acti 9 iATL4 Acti 9 iATLc Acti 9 iATLc+s Acti 9 iATLm Acti 9 iATLs Acti 9 iATLz Acti 9 iETL iTL 16 Acti 9 iATLc+c Acti 9 iATL24

Environment

Standards	EN 669-2-2 EN 669-1
Product Certifications	GOST CCC
Quality Labels	KEMA CEBEC NF IMQ VDE
Noise Level	60 dB
Ip Degree Of Protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	113.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12

Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	23.0 cm
Package 2 Weight	1.411 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.436 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Mercury Free	
✓	RoHS Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations