

Product data sheet

Specifications



standard analog output module STB - 0..20 mA - 2 O - 12 bits

STBACO1210

 **Discontinued on:** Sep 9, 2009

 **Discontinued**

Main

Range Of Product	Modicon STB distributed I/O solution
Product Or Component Type	Standard analog output module
Analogue Output Type	Current 0...20 mA
Analogue Output Number	2
Analogue Output Resolution	12 bits

Complementary

Analogue Output Current	0.02 A
Response Time	3 ms
Cold Swapping	Yes
Hot Swapping	Yes for standard NIMs
Fallback	State 0 basic NIMs User configurable standard NIMs
Data Format	IEC 61131-2 EN 61131-2
Update Time	25 ms
Conversion Time	900 ms at +/- 0.1 % of final value
Protection Type	Short-circuit protection
Integral Linearity	+/- 0.1 %FS
Differential Linearity	Monotonic
Absolute Accuracy Error	+/- 0.5 % of full scale per °C
Temperature Drift	+/-0.01 %/°C
Insulation Between Channels And Logic Bus	1500 V for 1 minute
Insulation Between Channels And Actuator Bus	30 V
Addressing Requirement	2 output words 1 word for configuring fallback status
Product Compatibility	Power distribution module STBPDT3100/3105 Mounting base STBXBA1000
[Us] Rated Supply Voltage	24 V DC
Supply	Power distribution module
Current Consumption	40 mA 5 V DC logic bus
Marking	CE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Overvoltage Category	II
Status Led	1 LED (Green) module status (RDY) 1 LED (Red) module error (ERR)
Depth	2.76 in (70 mm)
Height	0.55 in (13.9 mm)
Width	5.05 in (128.3 mm)
Net Weight	0.26 lb(US) (0.117 kg)

Environment

Product Certifications	CSA FM Class 1 Division 2 UL
Pollution Degree	2 IEC 60664-1
Operating Altitude	<= 6561.68 ft (2000 m)
Ip Degree Of Protection	IP20 conforming to EN 61131-2 class 1
Ambient Air Temperature For Operation	32...140 °F (0...60 °C) without derating
Ambient Air Temperature For Operation	32...140 °F without derating
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C) without derating
Ambient Air Temperature For Storage	-40...185 °F without derating
Relative Humidity	95 % 140 °F (60 °C) without condensation
Vibration Resistance	3 gn 58...150 Hz 35 x 7.5 mm symmetrical DIN rail 5 gn 58...150 Hz 35 x 15 mm symmetrical DIN rail +/-0.35 mm 10...58 Hz
Shock Resistance	30 gn 11 ms IEC 88 reference 2-27

Ordering and shipping details

Category	18215-ADVANTYS STB I/O
Discount Schedule	PC32
Gtin	00785901578666
Returnability	No
Country Of Origin	FR

Contractual warranty

Warranty	18 months
----------	-----------