Specification





# CANopen interface I/O block, Modicon TM7, IP67, 8 M8

TM7NCOM08B

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 795.00 USD

# Main

Range Of Product	Modicon TM7	
Product Or Component Type	CANopen interface I/O block	
Range Compatibility	Modicon LMC058 Modicon M258	
Enclosure Material	Plastic	
Bus Type	CANopen	
[Ue] Rated Operational Voltage	24 V DC	
Input/Output Number	8	
Input/Output Number Of Block	8 I/O	

# Complementary

Discrete Input Number	08 configurable by software	
Discrete Input Voltage	24 V	
Discrete Input Voltage Type	DC	
Discrete Input Current	4.4 mA	
Discrete Input Logic	Positive	
Discrete Output Number	08 configurable by software	
Discrete Output Voltage	24 V	
Discrete Output Voltage Type	DC	
Discrete Output Current	<= 0.5 A	
Discrete Output Type	Transistor	
Sensor Power Supply	24 V, 500 mA for all channels overload, short-circuit and reverse polarity protection	
Electrical Connection	1 male connector M12 - A coding - 5 ways CANopen bus IN 1 female connector M12 - B coding - 4 ways TM7 bus OUT 8 female connectors M8 - 3 ways sensor or actuator 1 male connector M8 - 4 ways power IN 1 female connector M8 - 4 ways power OUT	
Local Signalling	for bus diagnostic 2 LEDs for actuator power supply diagnostics 1 LED for sensor power supply diagnostics 1 LED	
Operating Position	Any position	
Fixing Mode	By 2 screws	
Net Weight	0.43 lb(US) (0.195 kg)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Environment**

Standards	IEC 61131-2	
Product Certifications	cURus ATEX II 3g EEx nA II T5 GOST-R C-tick	
Marking	CE	
Ambient Air Temperature For Operation	14140 °F (-1060 °C)	
Ambient Air Temperature For Storage	-13185 °F (-2585 °C)	
Relative Humidity	595 % without condensation or dripping water	
Pollution Degree	2 IEC 60664	
Ip Degree Of Protection	IP67 conforming to IEC 61131-2	
Operating Altitude	06561.68 ft (02000 m)	
Storage Altitude	0.009842.52 ft (03000 m)	
Vibration Resistance	7.5 mm constant amplitude 28 Hz)IEC 60721-3-5 Class 5M3 2 gn constant acceleration 8200 Hz)IEC 60721-3-5 Class 5M3 4 gn constant acceleration 200500 Hz)IEC 60721-3-5 Class 5M3	
Shock Resistance	30 gn 11 ms IEC 60721-3-5 Class 5M3	
Resistance To Electrostatic Discharge	6 kV in contact IEC 61000-4-2 8 kV in air IEC 61000-4-2	
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 0.082 Hz IEC 61000-4-3 0.91 V/m (1 V/m) 22.7 Hz IEC 61000-4-3	
Resistance To Fast Transients	2 kV IEC 61000-4-4 power supply) 1 kV IEC 61000-4-4 input/output) 1 kV IEC 61000-4-4 shielded cable)	
Surge Withstand For Dc 24 V Circuit	1 kV power supply (common mode) IEC 61000-4-5 0.5 kV power supply (differential mode) IEC 61000-4-5 1 kV unshielded links (common mode) IEC 61000-4-5 0.5 kV unshielded links (differential mode) IEC 61000-4-5 1 kV shielded links (common mode) IEC 61000-4-5 0.5 kV shielded links (differential mode) IEC 61000-4-5	
Electromagnetic Compatibility	EN/IEC 61000-4-6	
Disturbance Radiated/Conducted	CISPR 11	

# Ordering and shipping details

_	• • •
Category	US1PC1222532
Discount Schedule	PC12
Gtin	3595864092782
Returnability	No
Country Of Origin	AT

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.000 cm)
Package 1 Width	2.32 in (5.900 cm)
Package 1 Length	4.17 in (10.600 cm)
Package 1 Weight	7.65 oz (217.000 g)

Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	12.53 lb(US) (5.682 kg)

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>②</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free

#### **Certifications & Standards**


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	End of Life Information			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

#### TM7NCOM08B

#### Presentation

#### TM7 CANopen Interface I/O Block

#### Description



- (A) CANopen bus IN connector
- (B) TM7 bus OUT connector
- (C) 24 Vdc power IN connector
- (D) 24 Vdc power OUT connector
- (1) Input / Output connectors
- (2) Status and channel LEDs
- (3) CANopen address settings rotary switches

#### **Connector and Channel Assignments**


I/O connectors	Channel types	Channels	
1	Input/Output	10/Q0	
2	Input/Output	I1/Q1	
3	Input/Output	12/Q2	
4	Input/Output	13/Q3	
5	Input/Output	14/Q4	
6	Input/Output	15/Q5	
7	Input/Output	16/Q6	
8	Input/Output	17/Q7	

# TM7NCOM08B

**Dimensions Drawings** 


# TM7 Block, Size 1

#### **Dimensions**



# Mounting and Clearance


# **Spacing Requirements**



- 1 Straight cable
- 2 Elbowed cable


#### **Installation Guidelines**

#### TM7 Block on an Aluminium Frame



NOTE: Maximum torque to fasten the required M4 screws is 0.6 N.m (5.3 lbf-in).

#### TM7 Block on a DIN Rail




NOTE: Only size 1 (smallest) blocks can be installed on DIN rail with the TM7ACMP mounting plate.

#### TM7 Block Directly on the Machine

Drilling template of the block:

# TM7NCOM08B






- (1) Size 1
- (2) Size 2

The thickness of the base plate should be taken into consideration when defining the screw length.

# TM7NCOM08B



NOTE: Maximum torque to fasten the required M4 screws is 0.6 N.m (5.3 lbf-in).

# TM7NCOM08B

# Connections and Schema


# Wiring Diagram

# Pin Assignments for I/O Connectors

Connection	Pin	Designation
3 4	1	24 Vdc sensor / actuator supply
	3	0 Vdc
	4	DI/DO: input/output signal

#### **CANopen Pins and Connectors**

#### **Connector Assignments**



- (A) Field bus IN connector
- (B) and (B2) TM7 bus OUT connector M12
- (B1) CANopen bus OUT connector M12
- (C) 24 Vdc power IN connector
- (D) 24 Vdc power OUT connector
- (1) Address settings rotary switches
- (2) Status LEDs

#### Pin Assignments

Connectors	Pin	Designation
A 3	1	CAN_SHLD
	2	(CAN_V+)
$((\bullet,\bullet,\S)$	3	CAN_GND
	4	CAN_H
	5	CAN_L
B/B2 2 2 1	1	TM7 V+
	2	TM7 Bus Data
	3	TM7 0V
	4	TM7 Bus Data
	5	N.C.
D4	1	CAN_SHLD

# Product data sheet TM7NCOM08B


Connectors	Pin	Designation
	2	(CAN_V+)
	3	CAN_GND
	4	CAN_H
	5	CAN_L

Connectors	Pin	Designation
	1	24 Vdc main power
2 2 3	2	24 Vdc I/O power segment
	3	0 Vdc
	4	0 Vdc
D 2 1	1	24 Vdc I/O power segment
	2	24 Vdc I/O power segment
	3	0 Vdc
	4	0 Vdc

#### TM7NCOM08B

#### Wiring the Power Supply

Connections	2 Power Supplies
24 Vdc main power that generates power for TM7 power bus	PS1
24 Vdc I/O power segment	PS2




- (2) External fuse, Type T slow-blow, 1 A, 250 V <sup>1</sup>
- (3) External fuse, Type T slow-blow, 4 A max., 250 V
- PS1 External isolated main power supply, 24 Vdc
- PS2 External isolated I/O power supply, 24 Vdc

<sup>&</sup>lt;sup>1</sup> Fuse limited to 1 A per PDB, maximum fuse limited to 5 A with maximum 4 PDB interconnected. If less then 4 PDBs size the fuse in accordance with the number of PDBs.

### TM7NCOM08B

#### Performance Curves

# **Switching Inductive Load Characteristics**



- (1) Load resistance in  $\Omega$
- (2) Load inductance in H
- (3) Max. operating cycles / second