Product datasheet





Controller, Harmony SCU, Rear Module panel, Dig 16 inputs/10 outputs

HMISAC

Discontinued on: Nov 1, 2020



Main

Range Of Product	Harmony SCU
Product Or Component Type	Controller
Device Presentation	Rasic element

Complementary

Supply	External source
[Us] Rated Supply Voltage	24 V (20.428.8 V)DC
Immunity To Microbreaks	10 ms
Inrush Current	30 A
Power Consumption In W	15 W
Local Signalling	No indicator
Number Of Pages	Limited by internal memory capacity
Software Designation	SoMachine
Operating System	Harmony
Processor Name	CPU RISC
Processor Frequency	333 MHz
Memory Description	Flash NAND, 128 MB Internal data storage FRAM, 128 kB Application run DRAM, 128 MB
Integrated Connection Type	1 serial link - RJ45 - RS232/RS485 (rate: <= 115.2 kbits/s) 1 Ethernet TCP/IP - RJ45 1 USB 2.0 type mini B 1 USB 2.0 type A CANopen master bus - SUB-D 9
Realtime Clock	Built-in
Downloadable Protocols	Modbus Modbus TCP/IP CANopen
Fixing Mode	By 1 nut - diameter: Ø 22 mm, mounting on: 16 mm thick panel
Enclosure Material	PC/PBT
Shock Resistance	147 m/s² for 11 ms (on DIN rail) conforming to IEC 60068-2-27 294 m/s² for 6 ms (on panel mounting) conforming to IEC 60068-2-27
Vibration Resistance	+/- 3.5 mm (f = 59 Hz) conforming to IEC 60068-2-6 1 gn (f = 9150 Hz) conforming to IEC 60068-2-6

Life Is On Schneider Apr 19, 2024

Electromagnetic Compatibility	Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to IEC 61000-4-2
	Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to IEC 61000-4-2
	Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to IEC 61000-4-3
	Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (between analogue I/O and operating voltage) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 2 kV (relay wires) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (Ethernet line) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (COM line) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (CAN line) conforming to IEC 61000-4-4
	Surge immunity test - test level: 2 kV (power supply (common mode)) conforming to IEC 61000-4-5
	Surge immunity test - test level: 1 kV (power supply (differential mode)) conforming to IEC 61000-4-5
	Surge immunity test - test level: 1 kV common mode (digital I/O) conforming to IEC 61000-4-5
	Surge immunity test - test level: 0.5 kV differential mode (digital I/O) conforming to IEC 61000-4-5
	Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to IEC 61000-4-6
	Conducted emission - test level: 150 kHz30 MHz conforming to EN 55011 Radiated emission - test level: 30 MHz1 GHz conforming to EN 55011
Discrete Input Number	2 for fast input (normal mode) conforming to IEC 61131-2 Type 1 14 for digital input conforming to IEC 61131-2 Type 1
Discrete Input Voltage	24 V DC, discrete input logic: sink or source (positive/negative)
Number Of Common Point	1 for fast input (HSC mode) 2 for digital input
Discrete Input Current	7.83 mA for fast input 5 mA for digital
Input Impedance	4.7 kOhm 2.81 kOhm
Sensor Power Supply	1528.8 V DC >= 15 V, current (state 1): >= 5 mA <= 5 V, current (state 0): <= 1.5 mA
	1528.8 V DC >= 15 V, current (state 1): >= 2.5 mA <= 5 V, current (state 0): <= 1 mA
Configurable Filtering Time	0 ms no filter (none) 0.0040.04 ms bounce filter (latch/event and cumulative filter by step Nx0.5ms (64>=N>=2)) 312 ms integrator (none/run/stop)
Maximum Innut Fraguanay	
Maximum Input Frequency	100 kHz for fast input (encoder mode) - control type A/B 100 kHz for fast input - control type single phase 100 kHz for fast input - control type pulse/direction
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Shielded cable: <100 m for digital input Unshielded cable: <50 m for digital input
Connection Pitch	3.5 mm
Overvoltage Protection	With overvoltage protection
Isolation Between Channels And Internal Logic	500 V DC
Isolation Between Channels	None
Discrete Output Number	2 fast output (normal mode), output logic: source 8 digital output, output logic: source
Discrete Output Voltage	24 V DC (voltage limit: 19.228.8 V) with transistor discrete output(s) 24 V DC (voltage limit: 530 V) with relay discrete output(s) 220 V AC (voltage limit: 100250 V) with relay discrete output(s)

Input/Output Number	2 for fast input, terminal(s): FI0FI1
	14 for digital input, terminal(s): DI0DI13
	2 for fast output, terminal(s): FQ0FQ1
	8 for digital output, terminal(s): DQ0DQ7
Discrete Output Current	2 A 4 A), response time 5 ms with opening contact for digital output
	2 A 4 A), response time 2 ms with closing contact for digital output
	300 mA, response time 2 ms for fast output (normal mode)
	50 mA, response time 2 ms for fast output (PWM or PTO mode)
Insulation Resistance	> 10 MOhm between the I/O and internal logic
	> 10 MOhm between power supply and earth
Maximum Output Frequency	100 kHz for fast output (PTO mode)
	1 kHz for fast output (PWM mode)
Absolute Accuracy Error	+/- 0.1 % of full scale cyclic ratio 199% for fast output (PWM or PTO mode)
	1 % of full scale cyclic ratio 199% for fast output (PWM or PTO mode)
	+/- 5 % of full scale cyclic ratio 1090% for fast output (PWM or PTO mode)
	+/- 10 % of full scale cyclic ratio 2080% for fast output (PWM or PTO mode)
	+/- 15 % of full scale cyclic ratio 3070% for fast output (PWM or PTO mode)
 Height	50.65 mm
Width	128 mm
Depth	102 mm
Net Weight	0.359 kg
Environment Standards	FCC Class A
	ANSI/ISA 12-12-01
	UL 508
	IEC 61000-6-2
	EN 61131-2
	CSA C22.2 No 213 Class I Division 2
Product Certifications	GOST
	C-Tick
	KCC
	cULus 508
	cULus CSA 22-2 No 142
	cUL 1604 Class 1 Division 2
Marking	CE
Ambient Air Temperature For Operation	050 °C
Ambient Air Temperature For Storage	-2060 °C
Relative Humidity	585 % without condensation
Operating Altitude	<= 2000 m
Storage Altitude	010000 m
Maximum Pressure	8001114 hPa
Ip Degree Of Protection	IP20 (rear panel) conforming to IEC 60529 IP65 (front panel) conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X front panel

Packing Units

Environmental Characteristic

Pollution Degree

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.200 cm

2 conforming to IEC 60664

Corrosive gas free

Package 1 Width	19.000 cm
Package 1 Length	26.800 cm
Package 1 Weight	988.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.677 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Resource performance



Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

HMISAC


Dimensions Drawings

Dimensions




Mounting and Clearance

Recommended Mounting position




- (1) Horizontal mounting
- (2) Vertical mounting

No Recommended Mounting Position



Clearance




Keep adequate spacing for proper ventilation to maintain an ambient temperature between 0...50 °C (32...122 °F) for horizontal installation and 0...40 °C (32...104 °F) for vertical installation.

HMISAC


Connections and Schema

Wiring Diagram



(1) Slow-blow 2A type T fuse


Wiring Diagram of Digital Inputs



- (1) HSC inputs with pin assignment of terminal blocks C,D.
- (2) Digital inputs with pin assignment of terminal blocks C,D.

11

Wiring Diagram of Digital Outputs



- (1) Digital outputs with pin assignment of terminal blocks A,B.
- (2) PWM outputs with pin assignment of terminal blocks C,D.
- (L) Load