# **Product datasheet**

Specifications





### TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 12 A - 24 V DC coil

LC1D126BL

() Discontinued on: Jul 10, 2021

() Discontinued

#### Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 12 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 12 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

#### Complementary

Motor Power Kw	3 kW at 220230 V AC 50/60 Hz (AC-3)
	5.5 kW at 380400 V AC 50/60 Hz (AC-3)
	5.5 kW at 415 V AC 50/60 Hz (AC-3)
	5.5 kW at 440 V AC 50/60 Hz (AC-3)
	7.5 kW at 500 V AC 50/60 Hz (AC-3)
	7.5 kW at 660690 V AC 50/60 Hz (AC-3)
	3 kW at 220230 V AC 50/60 Hz (AC-3e)
	5.5 kW at 380400 V AC 50/60 Hz (AC-3e)
	5.5 kW at 415 V AC 50/60 Hz (AC-3e)
	5.5 kW at 440 V AC 50/60 Hz (AC-3e)
	7.5 kW at 500 V AC 50/60 Hz (AC-3e)
	7.5 kW at 660690 V AC 50/60 Hz (AC-3e)
	3.7 kW at 400 V AC 50/60 Hz (AC-4)
Motor Power Hp	0.5 hp at 115 V AC 50/60 Hz for 1 phase motors
	2 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	3 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	3 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	7.5 hp at 460/480 V AC 50/60 Hz for 3 phases motors
	10 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	25 A (at 60 °C) for power circuit
Thermal Current	10 A (at 60 °C) for signalling circuit

Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	105 A 40 °C - 10 s for power circuit
Current	210 A 40 °C - 1 s for power circuit 30 A 40 °C - 10 min for power circuit
	61 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	40 A gG at <= 690 V coordination type 1 for power circuit
	25 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit
Power Dissipation Per Pole	0.36 W AC-3 1.56 W AC-1
	0.36 W AC-1
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Overvoltage Category	111
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Electrical Durability	2 Mcycles 12 A AC-3 at Ue <= 440 V
	0.8 Mcycles 25 A AC-1 at Ue <= 440 V 2 Mcycles 12 A AC-3e at Ue <= 440 V
Control Circuit Type	DC low consumption
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC
	0.81.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	2.4 W (at 20 °C)
Hold-In Power Consumption In W	2.4 W at 20 °C
Operating Time	77 ±15 % ms closing
Time Constant	25 ±20 % ms opening
Time Constant	40 ms
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: lugs-ring terminals - external diameter: 8 mm Power circuit: lugs-ring terminals - external diameter: 8 mm
Tightening Torque	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5
	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5
	Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 8 mm M3.5
	Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5
	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5 Power circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1
	type mirror contact 1 NC conforming to IEC 60947-4-1

Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	

### Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	GL LROS (Lloyds register of shipping) GOST BV CSA UL RINA DNV CCC UKCA
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)
Height	77 mm
Width	45 mm
Depth	95 mm
Net Weight	0.485 kg

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	9.500 cm
Package 1 Length	12.000 cm
Package 1 Weight	538.000 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.314 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	141.024 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information